

YDS26

by Burndy
Catalog ID: YDS26

Prop 65 Notice

Hysplice, 2/0 (7, 12, 19) str., 6 in L, Full Tension Sleeve for Stranded Copper Conductors.

Features: Made Of Pure Copper Tubing, Designed To Develop The Full Rated Breaking Strength Of Hard Drawn Or Medium Hard Drawn Copper Conductor, Installed With Standard Tooling, Die Index: 166 Element A, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W166 Die, (12), Y35, Y750 Tool, U165/U459 Die, (6), Y45 Tool, U165/U459 Die With PT-6515 Adapter, (6), Y46 Tool, U165/U459 Die With PUADP-1 Adapter, (6), Conductor Type: Stranded Copper



Product Details

General

Application	For Stranded Copper Conductors
Connector Type	Splice
Die Index	166
Material	Copper
Oxide Inhibitor Type	Penetrox E
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS
UPC	781810564844

Dimensions

Dimension - A Outside Diameter inch	0.71 in
Dimension - B Length fraction	2-17/20 in
Dimension - B Length inch	2.85 in
Dimension - B Outside Diameter inch	0.71 in
Dimension - L Length Overall mm	151 mm
Dimension - Length Overall inch	5.95 in
Dimension - Outside Diameter inch	0.71 in

Conductor Related

Conductor - Copper Str Size	2/0 AWG
-----------------------------	---------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)