

YDS28

by Burndy
Catalog ID: YDS28

Prop 65 Notice

Full Tension Sleeve for Stranded CU Conductors, 4/0 Str., 6.91 in Length, 168 Index.

Features: Made Of Pure Copper Tubing, Designed To Develop The Full Rated Breaking Strength Of Hard Drawn Or Medium Hard Drawn Copper Conductor, Installed With Standard Tooling, Die Index: 168 Element A, Conductor Type: Stranded Copper, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U168 Die, (9), Y45 Tool, U Die With Adapter PT-6515, Y46 Tool, U Die With Adapter PUADP-1, Y48B Tool, C168 Die, (3), Y60BHU Tool, L168 Die, (3)



Product Details

General

Application	For Stranded Copper Conductors
Connector Type	Splice
Die Index	168
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	3
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS
UPC	781810821015

Dimensions

Dimension - B Length inch	3.27 in
Dimension - L Length Overall mm	176 mm
Dimension - Length Overall inch	6.91 in
Dimension - Outside Diameter inch	0.89 in

Conductor Related

Conductor - Copper Str Size	4/0 AWG
-----------------------------	---------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)