

YDS2CA

by Burndy
Catalog ID: YDS2CA

Prop 65 Notice

Full tension aluminum splice with staked in cable stop. ANSI C199.4 Class 1 (Full Tension), Conductor: 2(7).

Features: Full-Tension HYSPLICE Sleeve Made Of Aluminum Tubing With Staked-In Cable Stop, Sizes 1/0 And Larger Tapered For Gradual Transition Of Stress, Installed With HYSPLICE Tools And Dies, Pre-Filled With PENETROX Joint Compound And Capped, Die Index: 693 Element A, 6A EEL, Conductor Type: Aluminum, Tools, Die Set Catalog Number, And (number Of Crimps): MD7, MD6 Tool, W163 Die, (6), Y35, Y750 Tool, U163 Die, (2), Y45 Tool, U Die With Adapter PT-6515, Y46 Tool, U Die With Adapter PUADP-1



Product Details

General

Application	For All Aluminum Compressed And Compact Conductors
Connector Type	Splice
Die Index	163
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-A
UPC	781810015339
UPC 12 Digit	7818100153399

Dimensions

Dimension - B Length fraction	1-22/25 in
Dimension - B Length inch	1.88 in
Dimension - Inside Diameter inch	1 in
Dimension - L Length Overall mm	99 mm
Dimension - Length Overall inch	3.88 in
Dimension - Outside Diameter inch	0.5 in

Conductor Related

Conductor - ACAR Str Size	2 (7) AWG
Conductor - ACAR Str Size Range	2 (7) AWG
Conductor - ACSR Cmpt Size	2 AWG
Conductor - ACSR Cmpt Size Range	2 AWG
Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG

Conductor Type	<ul style="list-style-type: none">• ACSR C Str-Size• AL C Str-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)