

YGS28

by Burndy
Catalog ID: YGS28

Prop 65 Notice

Grounding Irreversible Compression Splices, 4/0 str., Grounding Irreversible Compression Splices.

Features: Irreversible Compression HYLINK Ground Splices Specifically Designed For Grounding Applications, Each Conductor Element Has An Inspection Probe Hole And A Center Stop To Ensure Proper Cable Insertion, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, UL486A Listed, Prefilled With PENETROX Compound And Strip Sealed, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD7-34R, OUR840 Tool, W28VT, X28RT Die, (4), Hydraulic: Y35, Y39, Y750, PAT750 Tool, U28RT Die, (2), Y45 Tool, U28RT Die With PT6515 Adapter, Y46 Tool, U28RT Die With PUADP-1 Adapter, (2), Die Index: 15 Element A, Conductor Type: Stranded Copper



Product Details

General

Application	For Direct Burial In Earth Or Concrete
Connector Type	Splice
Die Index	15
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splices
UPC	781810220429
UPC 12 Digit	7818102204299

Dimensions

Dimension - B Length fraction	1-7/20 in
Dimension - B Length inch	1.57 in
Dimension - L Length Overall mm	86 mm
Dimension - Length Overall inch	3.37 in
Dimension - Outside Diameter inch	0.69 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	4/0 Str.
Conductor - Copper Str Size Range	4/0 Str.
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • UL 486A-486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL 486A-486B • UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)