



YSV6CL

by Burndy
Catalog ID: YSV6CL

Copper Compression Splice, AN 6, 1.12" Splice Length, Short Barrel, Tin Plated.

Features: HYLINK Type YSV-L Seamless Splice Connector Is Used To Splice Type AN Aircraft Cables Plus Commercial Stranded And Solid AWG Conductors, Suitable For Aircraft, Light Duty Industrial And General Purpose Applications, Tools, Die Nest Catalog Number, Die Indentor Catalog Number: HYPRESS: H35, Y35BH, Y39, Y39BH Tool, UV6L Die Nest, Y34PLA Die Indentor, Y35P3 Indentor Adaptor, Conductor Type: Commercial/Aircraft Stranded Copper, Installation Tool: Ratchet: Y1MRTC, MR4C Tool, HYTOOL: Type AH, Aircraft, Cable - MY28 Tool, All Others: MY29-3, MY29-11 Tool, 1 Crimp, Wire Strip Length: 1/2 IN, Insulation Support: No

Product Details

General

Application	For Aircraft, Light Duty Industrial And General Purpose Applications
Connector Type	Splice
Die Index	39
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810543856

Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - L Length Overall mm	28 mm
Dimension - Length Overall inch	1.12 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Strip Length inch	5/8 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size	6 AWG
Conductor - Copper Str Aircraft Size	AN 6
Conductor - Copper Str Size	6 AWG

Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size• CU C Str Aircraft-Size
----------------	--

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)