

TP108F

by Burndy
Catalog ID: TP108F

Prop 65 Notice

Insulated Brazed Fork Terminal, Insulated Brazed Fork Terminal, Smooth Entry, #12-#10, 600V, #6-#8 Stud, Vinyl Insulated, Tin Plated.

Features: The Type TP-F Is A Fork Tongue Variation Of The TP Design And Makes Installation Easier, 600 V Maximum, 105 DEG C Max, Fork Tongue Design: Faster Installation-Screw Needs Only To Be Loosened For Termination, Installation Tool: MR15, M8ND Tool With N10ET-23 Die, Insulation Diameter (maximum): 0.26 IN, Bulk Catalog Number: BA10EF8, Temperature Rating: 105 DEG C Maximum, Tape Mounted Catalog Number: BA10EF8M, Color Code: Yellow, Wire Strip Length: 19/64 IN, Finish: Electro-Tin Plated, Wire Insulation Grip: No



Product Details

General

Application	For Commercial And Light Duty Industrial Control And Power Circuit Applications
Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	TP-F
UPC	781810710685
UPC 12 Digit	7818107106855

Dimensions

Cable Insulation Diameter Maximum	0.260 in
Dimension - B Length fraction	17/50 in
Dimension - B Length inch	0.34 in
Dimension - Hole Size fraction	8/47
Dimension - Hole Size inch	0.17 in
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	0.98 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	#8

Dimension - Z inch	0.26 in
--------------------	---------

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)