



YA44

by Burndy Catalog ID: YA44

Prop 65 Notice

Copper Compression Lug, 1 Hole w/o Inspection Window, 1000 kcmil, 5/8" Stud, Long Barrel, Electro Tin Plated.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Finish: Electro-Tin Plated, Tongue Angle: Straight, Wire Strip Length: 3-1/16 IN, Die Index: 27, Temperature Rating: 90 DEG C, Color Code: White, Tools, Die Set Catalog Number, And (number Of Crimps): Hydraulic: Y46 Tool, P44RT Die, (4), Conductor Type: Commercial Stranded Copper, Dieless Tools (number Of Crimps): Y644HS Tool, (1), Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (4)

Product Details

General

Application	For Code Conductor		
Color Code	White		
Connector Type	Terminal		
Die Index	27		
Feature - Barrel Style	Chamfered		
Feature - Barrel Type	Long		
Material	Copper		
Physical Attribute - Number of Holes	1		
Physical Attribute - Tongue Type	Standard		
Plated	Y		
Plating Type	Tin - Electro Plated		
Sub Brand	HYLUG		
Temperature Rating	194		
Trade Name	HYLUG™		
Туре	Long Barrel, Tin Plated		
UPC	781810522950		
UPC 12 Digit	7818105229500		

Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3.00 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8 in
Dimension - D inch	1.33 in
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	18 mm
Dimension - L Length Overall mm	138 mm
Dimension - Length Overall inch	5.45 in

Dimension - N inch	0.66 in	
Dimension - Outside Diameter inch	1.50 in	
Dimension - Pad Width inch	2.19 in	
Dimension - Strip Length inch	3-1/16 in	
Dimension - Stud Size inch	5/8 in	
Dimension - Z inch	0.67 in	
Physical Attribute - Tongue Angle	Straight	

Electrical Ratings

Rating - KVA	35 kV	
Rating - Minimum Voltage	600	
Voltage - Maximum	35000	

Conductor Related

Conductor - Copper Str Size	1000 kcmil	
Conductor - Copper Str Size Range	1000 kcmil	
Conductor - Material	Copper	

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	СМ
UL Listed	Yes

Logistics

Minimum Pack Quantity	1	
1 minimum r den dedrittey	•	

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)