

## Stringlights Metal & Plastic Guards

For tough, temporary lighting shipped complete with guards to place in your own bulbs, our stringlights can't be beat. The rugged cable is high visibility yellow and can withstand the toughest treatment. The TLS has hanging holes on each socket allowing installation with either spikes or S-hooks. Each model comes standard with metal or plastic guards to deter theft and a connector, (TLS-100CG14LED does NOT have a connector).

\*See tables below for models and specifications

## Replacement Guard:

P/N TLS-SJ14 (plastic)



## Replacement Guard:

P/N TLS-MGC (metal)



## **KEY BENEFITS**

- Incredibly durable design will ensure long term use wiwthout damage or downtime.
- Can be linked together for longer runs.
- Highly visible yellow cable with grounding.



SPECIFICATIONS					
REPLACEMENT LED LAMP	Part Number: TLS-LEDCG-P2 • Fits standard Edison socket				
RATING	Suitable for wet conditions				



**Bulb:** Socket are rated for a maximum 120V 150W A23 style bulb. Do not use A19 bulbs



PART NO.	LENGTH	# OF SOCKETS	GUARD	WEIGHT	CABLE	CONNECTOR
TLS-100CG14	100'	10	Plastic	15 lbs	14/2 SJTW	NO
TLS-50SJ14	50'	5	Plastic	9 lbs	14/3 SJTOW	YES
TLS-100SJ14	100'	10	Plastic	16 lbs	14/3 SJTOW	YES
TLS-50MGSJ14	50'	5	Metal	11 lbs	14/3 SJTOW	YES
TLS-100MGSJ14	100'	10	Metal	20 lbs	14/3 SJTOW	YES



