

Project Name

Location

Prepared By



SATCO S11409

9.8A19/LED/50K/120V/ECO/ND

Notes

[www] 01-25-2021 01:02:00

General

Status	Active
Watts	9.8
Incandescent Equivalent	60
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80
Lumens	800
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	10000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60 Hz
Power Factor	0.55
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

Physical

MOL	4.34
MOD	2.38
Housing Color	White

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
California Status	Non-Compliant
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
SDS Sheet	LED_Lamp