

Project Name

Location

Prepared By



## SATCO S11405

5.8A19/LED/50K/120V/ECO/ND

Notes

[www] 01-19-2021 00:51:04

### General

Status	Active
Watts	5.8
Incandescent Equivalent	40
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80
Lumens	450
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	10000
Lamp Type	Type A
Technology	LED

### Electrical

Operating Frequency	60 Hz
Power Factor	0.55
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

### Physical

MOL	4.34
MOD	2.38
Housing Color	White

### Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

### Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
California Status	Non-Compliant
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
SDS Sheet	LED_Lamp