

S200
K

S200 480Y/277VAC Supplementary Protectors

pro M compact


K UL 1077 CSA C22.2 - N° 235
IEC-947-2
Cable & equipment protection



S201-K15




S202-K15



S203-K15

K



Rated current	Catalog number	List price	Delivery class	Sugg. order qty	Wgt. kg (1 pc.)
1 pole					
0.5	S201-K0.5				
1	S201-K1				
1.6	S201-K1.6				
2	S201-K2				
3	S201-K3				
4	S201-K4				
5	S201-K5				
6	S201-K6				
8	S201-K8		A	10	0.125
10	S201-K10				
13	S201-K13				
15	S201-K15				
16	S201-K16				
20	S201-K20				
25	S201-K25				
30	S201-K30				
32	S201-K32				
40	S201-K40				
50	S201-K50				
60	S201-K60				
63	S201-K63				

Rated current	Catalog number	List price	Delivery class	Sugg. order qty	Wgt. kg (1 pc.)
1 pole + neutral					
0.5	S201-K0.5NA				
1	S201-K1NA				
1.6	S201-K1.6NA				
2	S201-K2NA				
3	S201-K3NA				
4	S201-K4NA				
6	S201-K6NA				
8	S201-K8NA				
10	S201-K10NA		C	5	0.250
13	S201-K13NA				
16	S201-K16NA				
20	S201-K20NA				
25	S201-K25NA				
32	S201-K32NA				
40	S201-K40NA				
50	S201-K50NA				
63	S201-K63NA				

Rated current	Catalog number	List price	Delivery class	Sugg. order qty	Wgt. kg (1 pc.)
2 pole					
0.5	S202-K0.5				
1	S202-K1				
1.6	S202-K1.6				
2	S202-K2				
3	S202-K3				
4	S202-K4				
5	S202-K5				
6	S202-K6				
8	S202-K8				
10	S202-K10		A	5	0.250
13	S202-K13				
15	S202-K15				
16	S202-K16				
20	S202-K20				
25	S202-K25				
30	S202-K30				
32	S202-K32				
40	S202-K40				
50	S202-K50				
60	S202-K60				
63	S202-K63				

Rated current	Catalog number	List price	Delivery class	Sugg. order qty	Wgt. kg (1 pc.)
3 pole					
0.5	S203-K0.5				
1	S203-K1				
1.6	S203-K1.6				
2	S203-K2				
3	S203-K3				
4	S203-K4				
5	S203-K5				
6	S203-K6				
8	S203-K8				
10	S203-K10		A	1	0.375
13	S203-K13				
15	S203-K15				
16	S203-K16				
20	S203-K20				
25	S203-K25				
30	S203-K30				
32	S203-K32				
40	S203-K40				
50	S203-K50				
60	S203-K60				
63	S203-K63				

Rated current	Catalog number	List price	Delivery class	Sugg. order qty	Wgt. kg (1 pc.)
3 pole + neutral					
0.5	S203-K0.5NA				
1	S203-K1NA				
1.6	S203-K1.6NA				
2	S203-K2NA				
3	S203-K3NA				
4	S203-K4NA				
6	S203-K6NA				
8	S203-K8NA				
10	S203-K10NA		C	1	0.500
13	S203-K13NA				
16	S203-K16NA				
20	S203-K20NA				
25	S203-K25NA				
32	S203-K32NA				
40	S203-K40NA				
50	S203-K50NA				
63	S203-K63NA				

Rated current	Catalog number	List price	Delivery class	Sugg. order qty	Wgt. kg (1 pc.)
4 pole					
0.5	S204-K0.5				
1	S204-K1				
1.6	S204-K1.6				
2	S204-K2				
3	S204-K3				
4	S204-K4				
6	S204-K6				
8	S204-K8				
10	S204-K10		C	1	0.500
13	S204-K13				
16	S204-K16				
20	S204-K20				
25	S204-K25				
32	S204-K32				
40	S204-K40				
50	S204-K50				
63	S204-K63				

Delivery Class

- A** - Standard item, stock to 2 weeks lead time
- B** - Stock to 4 weeks lead time
- C** - 6 to 8 week lead time