



PROJECT	TYPE
---------	------

CATALOG NUMBER
----------------

### FEATURES

- 120V operation (remote power supply not required)
- 90+ CRI
- Dimmable (see [www.gmlighting.net](http://www.gmlighting.net))
- Wet location
- Available in white only
- 4" and 6" Square (nominal)
- 5" and 8" Round (nominal)
- 3000K and 4000K

### ELECTRICAL

- 120V (remote power supply not required)
- 10W and 15W
- 50,000 hour LED life

### OPTICS

- 3000K/4000K
- 600 / 650 / 900 / 950 lumens
- 90+ CRI

### LABEL

- ETL
- Energy Star

### WARRANTY

- 5 year warranty



### PRODUCT DESCRIPTION

Shallow mount (5/8" depth) surface mount LED light squares and discs that feature Edge-Lit Technology, enabling diode-free imaging (no hot spots) across the face of the fixture. Mounts directly to junction box by others.

### ORDERING INFORMATION

Catalog No.	Nominal Dimensions	Wattage	Lumens	CRI	Color Temp.*
GM-RND5-30-WH	5" Dia. Disc x 5/8"D	10W	600	90+	3000K
GM-RND5-40-WH	5" Dia. Disc x 5/8"D	10W	650	90+	4000K
GM-RND8-30-WH	8" Dia. Disc x 5/8"D	15W	900	90+	3000K
GM-RND8-40-WH	8" Dia. Disc x 5/8"D	15W	950	90+	4000K
GM-SLD4-30-WH	4" Sq. x 5/8"D	10W	600	90+	3000K
GM-SLD4-40-WH	4" Sq. x 5/8"D	10W	650	90+	4000K
GM-SLD6-30-WH	6" Sq. x 5/8"D	15W	900	90+	3000K
GM-SLD6-40-WH	6" Sq. x 5/8"D	15W	950	90+	4000K

\* Kelvin temperature (color) ±200K

### RETROFIT KITS

Catalog No.	Description
GM-SLD4/5-RKT	Retrofit kit for 4" Square and 5" Round GeoTask
GM-SLD6/8-RKT	Retrofit kit for 6" Square and 8" Round GeoTask

