











4" LINE VOLTAGE TRIM SERIES WALL WASH/PINHOLE/SLOT APERTURE

Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

| Trim Series | Dimensions | Aperture | Catalog No. | Housing/Lamp Compatibility |
|---|---|---------------------------------|----------------------------|---|
|  Adjustable Scoop |  5" | | 16-WH - White Trim | IC1/IC1W/IC1S/IC1P/TC1/TC1S/TC1R: 25W R14, 40W R16 (Intermediate Screw Base) APT1: 40W R14, 40W R16 (Intermediate Screw Base) |
| | | Adjustment: 50° Vertical | | |
|  Adjustable Scoop |  5" | | 446-WH - White Trim | IC1P: 50W MR16, 50W ES16 120V GU10 Base (Requires GU10-WHIP) TC1/TC1S/TC1R: 50W MR16, 50W PAR16 50W ES16 120V GU10 Base (Requires GU10-WHIP) APT1: 50W MR16, 50W PAR16, 50W ES16 GU10 Base (Requires GU10-WHIP) |
| | | Adjustment: 40° Vertical | | |
|  Pinhole with Integral Shield |  5" | 2" | 13-WH - White Trim | IC1/IC1W/IC1S: 30W R20, 35W PAR20 IC1P/TC1/TC1S/TC1R: 50W PAR20, 50W R20 IC1P: 40W K19 ICPL426 Series: 26W, ICPL418 Series: 18W, ICPL413 Series: 13W IC1LEDG3/IC1RLEDG3 Series APT1: 50W PAR20, 50W R20 |
| | | | | |
|  Adjustable Slot Aperture |  5" | 1 1/2" x 2 1/8" Oblong | 445-WH - White Trim | IC1P: 50W MR16, 50W ES16 120V GU10 Base (Requires GU10-WHIP) TC1/TC1S/TC1R: 50W MR16, 50W PAR16, 50W ES16 120V GU10 Base (Requires GU10-WHIP) APT1: 50W MR16, 50W PAR16, 50W ES16 GU10 Base (Requires GU10-WHIP) |
| | | Adjustment: 40° Vertical | | |

