

RL431

4" LED RETROFIT DIE-CAST ALUMINUM LENSED BAFFLE

SAME DAY
SHIPPING AVAILABLE



CRI 90+ , 85+

COLOR QUALITY 3-Step MacAdam Ellipses

LUMEN OUTPUT 650 Lumens

LUMEN PER WATT Up to 60

CCT 27K, 30K, 35K, 40K, 50K

OPTIC 45° Cut-Off

WARRANTY 5 Years

CERTIFICATIONS

- cULus
- RoHS
- IECC

- New York state
- UL/cUL Listed for Wet
- UL/cUL Listed for Damp Location

- California Title 24
- Washington state
- LM79/LM80

UNIQUELY ENGINEERED FOR NEW AND EXISTING CONSTRUCTION

The RL431 is the newest, most efficient, and advanced LED retrofit modules from ELITE Lighting. It's unique design delivers color quality above a 90 CRI rating. The color matching has never been so close, with a binning as low as 3 MacAdams ellipses. The RL431 LED retrofit meet all new mandatory California Title 24 requirements.

The Elite RL431 LED Module has been engineered for new constructions to meet Title-24's 'No Edison Socket' mandate. The Elite LED Module system works in our dedicated (LD4IC-AT, LD4-AT, LD4R-AT) housings and our existing 4" incandescent housings (or standard B4IC-AT, B4-AT and B4R-AT) but is also suitable for use in most 4" recessed downlight housings in the market.

INPUT VOLT.	INPUT FREQ.	THD	POWER FACTOR	INPUT POWER	LUMENS
120	50/60Hz	<20%	>0.9	10W(+/-5%)	650

DURABILITY

Our die-cast system pulls the heat from the LED chip, allowing the continued cool operation for years. Our LED driver is rated for 50 to 60 Hz at 120V input, and produces less than 20% THD, has a power factor between 0.90 and 1.00 and is thermal protected for additional safety.

DIMMABLE


The Elite LED Module is dimmable down to 15% of initial light output with compatible dimmers. Consult factory for complete list of compatible dimming systems.

OUR WORD

The Elite LED lighting system carries a five-year carefree warranty for parts and components. (Labor not included)

FEATURES

- Over 650 usable lumens are directed from the luminaire to the work surface
- Greater light output than a 18W CFL or a 50W BR20 while consuming less than 10W of power
- Rated at 90+ CRI to meet California Title-24 strict compliance standards
- Life tested to ensure light output up to 50,000 hours of operation to L70
- Glare reducing cut-off angle of 55 degrees
- High performance optic hides LED chip image but still delivers an even beam of light
- Elite's highly selective LED chips produce zero ultraviolet and virtually no infrared light
- Tested to LM-79 and LM-80 standards
- UL listed for safety



INSTALLATION

- Socket adapter removes from module, allowing installation to be quick and easy. Simply screw in the adapter and plug in the module. Turning off the entire module is not required.
- Utilizes industry standard friction blades, installs in most 4" incandescent down lights. Insert friction blades into can and press trim to ceiling.

LED

4"

4 INCH LED RETROFIT MODULE

RL431

4" LED RETROFIT DIE-CAST ALUMINUM LENSED BAFFLE

R20 Lamp



Before

RL428 LED Retrofit Series



After


Elite's innovative LED retrofit downlight modules deliver the brightest, most beautiful and most energy efficient ambient lighting to replace any lamp type on your existing fixture.

Example: **RL431-650L-DIMTR-120-30K-90-W-WH**

TYPE	650L SERIES	CCT	CRI	FINISH	OPTION	TRIM OPTIONS	
RL431 (Baffle)	<input type="checkbox"/> 650L-DIMTR-120	<input type="checkbox"/> 27K <input type="checkbox"/> 30K <input type="checkbox"/> 35K <input type="checkbox"/> 40K <input type="checkbox"/> 50K (85 CRI only)	<input type="checkbox"/> 90 <input type="checkbox"/> 85	<input type="checkbox"/> W-WH	<input type="checkbox"/> GU24SA GU24 SOCKET ADAPTER	BT (Baffle Trim) <input type="checkbox"/> RL431-BT-BZ-BZ <input type="checkbox"/> RL431-BT-CP-CP <input type="checkbox"/> RL431-BT-P-BK <input type="checkbox"/> RL431-BT-P-WH <input type="checkbox"/> RL431-BT-SN-SN	RT (Reflector Trim) <input type="checkbox"/> RL431-RT-BZ-BZ <input type="checkbox"/> RL431-RT-CL-WH <input type="checkbox"/> RL431-RT-CL-CH <input type="checkbox"/> RL431-RT-CP-CP <input type="checkbox"/> RL431-RT-MB-BK <input type="checkbox"/> RL431-RT-MB-WH <input type="checkbox"/> RL431-RT-RG-WH <input type="checkbox"/> RL431-RT-SHZ-SHZ <input type="checkbox"/> RL431-RT-SHZ-WH <input type="checkbox"/> RL431-RT-SN-SN <input type="checkbox"/> RL431-RT-SN-WH <input type="checkbox"/> RL431-RT-W-WH

AVAILABLE COLOR INSERTS FOR RL431 - 4" RETROFIT

BAFFLES




RL431-BT-P-BK



RL431-BT-BZ-BZ



RL431-BT-SN-SN



RL431-BT-P-WH



RL431-BT-CP-CP

REFLECTORS



RL431-RT-SHZ-WH



RL431-RT-RG-WH



RL431-RT-CP-CP



RL431-RT-BZ-BZ



RL431-RT-CL-WH



RL431-RT-W-WH



RL431-RT-SHZ-SHZ



RL431-RT-MB-WH



RL431-RT-SN-SN



RL431-RT-MB-BK



RL431-RT-CL-CH

Ordering Guide for Compatible Housing

IC - New Construction	Non-IC New Construction	IC - For Remodel	Non-IC For Remodel
LD4IC-AT	LD4-AT	LD4RIC-AT	LD4R-AT
HLD4IC-AT	HLD4-AT		HLD4R-AT
B4IC-AT	B4-AT		B4R-AT

*RECOMMENDED DIMMERS FOR ELITE RL431 LED SYSTEM

LUTRON DIMMERS

DIMTR

Diva DVCL-153P
 Skylark CTCL-153P
 Nova N-600
 NovaT NT-600
 Skylark S-600
 Ariadni AY-600P
 Nova NTLV-600
 Nova NLV-600

Maestro MRF2-6ND
 NovaT NTLV-600
 Diva DVELV-300P
 Skylark SELV-300P
 Nova NELV-450