

M12™ LED Metal Flashlight Kit

2355-21 (2355-20 Tool-Only)

Specifications:

opoomoa mono.	
Lumens	800 / 325 / 800
Modes	High, Medium, Strobe
Beam Distance	375 yd / 343 m
Beam Focus	Slide, Spot/Flood
Moisture Resistance	IP54
Structure	6000 Series Aluminum, Type II Anodize Finish 9"
Length	9"
Weight	1.2 lbs

Includes: (1) M12[™] REDLITHIUM[™] Compact Battery Pack, Lanyard, Charger



M12™ LED Spot Light

2353-20

Specifications:

Lumens	750 / 400 / 750
Modes	High, Low, Strobe
Beam Distance	700 yd / 640 m
Moisture Resistance	IP54
Length	6-1/8"
Weight	1.4 lbs

Battery and Charger Sold Separately

Includes: Lanyard



M12™ LED Lantern/Flood Light

2362-20

Specifications:	
Lumens	400 / 200 / 40 / 400
Modes	High, Medium, Low, Strobe
Beam Pattern	Adjustable 180° – 360°
Moisture Resistance	IP54
Hands-Free	2 Hooks for Hanging
USB Charger	2.1A USB Charging Port
Length	10-1/2"
Weight	1.0 lb



M12™ ROVER™ LED Flood Light

2364-20

Specifications:

•	
Lumens	1,000 / 400 / 200
Modes	High, Medium, Low
Hands Free	Integrated Magnet, Spring Loaded Clamp
Moisture Resistance	IP54
Length	7-1/2"
Weight	2.2 lbs

Battery and Charger Sold Separately



M12™ LED Stick Light

2351-20

Specifications:

•	
Lumens	220
Hands-Free	Multi-Position Stainless Steel Hook
Moisture Resistance	IP54
Length	9-1/4"
Weight	0.6 lbs

Battery and Charger Sold Separately

Related Accessory: 49-24-2351 M12[™] Stick Light Magnet Holds light to metal surfaces for hands-free use

M12™ LED Work Light

49-24-0146

Specifications:

Specifications:		
Lumens	100	
Hands-Free	Integrated Magnet	
Head Rotation	90°	

Battery and Charger Sold Separately



M12™ Heated Jacket Kit Black 201B-21 (201B-20 Jacket-Only)

Grey 201G-21 (201G-20 Jacket-Only) Red 201R-21 (201R-20 Jacket-Only) Camo 221C-21 (221C-20 Jacket-Only)

Specifications:

specifications.	•	CA XX
Heating Elements	5 (Chest, Back, Pockets)	
Heat Settings	3 (High, Medium, Low)	
Run-Time	Up to 8 Hours	
Outer Material	TOUGHSHELL™ Stretch	Polyester
Wind/Water Resistant	Yes	
USB Charger	2.1A	
Washer/Dryer Safe	Yes	

Includes: (1) M12™ REDLITHIUM™ 2.0 Compact Battery Pack, M12[™] Power Source, Charger

Available Sizes: S, M, L, XL, 2X, 3X



3

M12™ Heated Vest Kit

Black 271B-21 (271B-20 Vest-Only)

Specifications:		
	Heating Elements	3 (Chest, Back)
	Heat Settings	3 (High, Medium, Low)
	Run-Time	Up to 6 Hours
	Outer Material	GRIDIRON™ Ripstop Polyester
	Inner Lining	Thermal Fleece
	Wind/Water Resistant	Yes
	Washer/Dryer Safe	Yes

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, M12™ Battery Holder, Charger

Available Sizes: S, M, L, XL, 2X, 3X

M12™ Heated Hoodie Kit

Black 301B-21 (301B-20 Hoodie-Only) Grey 301G-21 (301G-20 Hoodie-Only) Red 301R-21 (301R-20 Hoodie-Only)

Specifications:

Heating Elements	3 (Chest, Back)
Heat Settings	3 (High, Medium, Low)
Run-Time	Up to 6 Hours
Outer Material	Cotton/Polyester Blend
Inner Lining	Thermal Waffle Weave
Washer/Dryer Safe	Yes

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, M12™ Battery Holder, Charger

Available Sizes: S, M, L, XL, 2X, 3X

M12™ Heated 3-in-1 Jacket Kit*

Black 251B-21 (251B-20 3-in-1 Jacket-Only)

Specifications: 251B		
Heating Elements (in Hoodie)	3 (Chest, Back)	4
Heat Settings	3 (High, Medium, Low)	
Run-Time	Up to 8 Hours	
Outer Material	GRIDIRON™ Ripstop Polyester	
Wind/Water Resistant	Yes	
USB Charger	2.1A	
Washer/Dryer Safe	Yes	

Includes: (1) M12™ REDLITHIUM™ 2.0 Compact Battery Pack, M12™ Power Source, Charger

Available Sizes: S, M, L, XL, 2X, 3X *M12™ Heated 3-in-1 Jacket is made up of (2) pieces: heated hoodie and durable outer shell.



Black 231B-21

Specifications:

Heating Elements	4 (Back, Collar, Pockets)
Heat Settings	3 (High, Medium, Low)
Run-Time	Up to 8 Hours
Outer Material	Polyester Soft Shell
Wind/Water Resistant	Yes
USB Charger	2.1A
Washer/Dryer Safe	Yes

Includes: (1) M12[™] REDLITHIUM[™] 2.0 Compact Battery Pack, M12™ Power Source, Charger

Available Sizes: S, M, L, XL, 2X

M12™ Heated Gear Accessory

Compatible with all M12[™] Heated Gear

49-24-2301 M12™ Heated Jacket 12V DC Plug Adapter



22

Realtree Xtra © and Realtree MAX-1 © 2017 of Jordan Outdoor Enterprises, Ltd., all rights reserved