

M18 FUEL
1/4" Hex Impact Driver w/ ONE-KEY™ Kit

2757-22, 2757-22CT (2757-20 Tool-Only)

Specifications:

Fastening Torque	1,800 in-lbs
IPM	0 – 3,700
RPM	0 – 3,000
DRIVE CONTROL™	4-Mode (Customizable)
Chuck Type	1/4" Hex
Length	5-1/4"
Weight	4.0 lbs

Includes: 2757-22 (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case; 2757-22CT Includes (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs



M18 FUEL
1/4" Hex Impact Driver Kit

2753-22, 2753-22CT (2753-20 Tool-Only)

Specifications:

Fastening Torque	1,800 in-lbs
IPM	0 – 3,700
RPM	0 – 3,000
DRIVE CONTROL™	4-Mode
Chuck Type	1/4" Hex
Length	5-1/4"
Weight	3.9 lbs

Includes: 2753-22 (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case; 2753-22CT Includes (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs



M18™ 1/4" Hex Brushless Impact Driver Kit

2750-22CT (2750-20 Tool-Only)

Specifications:

Fastening Torque	1,500 in-lbs
IPM	0 – 3,600
RPM	0 – 2,900
Chuck Type	1/4" Hex
Length	5-3/8"
Weight	3.1 lbs

Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Capacity Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case



M18 FUEL
SURGE™ 1/4" Hex Hydraulic Driver Kit

2760-22, 2760-22CT (2760-20 Tool-Only)

Specifications:

Sustained Fastening Torque	450 in-lbs
IPM	0 – 4,000
RPM	0 – 3,000
DRIVE CONTROL™	4-Mode
Length	5"
Weight	3.9 lbs

Includes: 2760-22 (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case; 2760-22CT Includes (2) M18™ REDLITHIUM™ 2.0 Battery Packs



M18™ 1/4" Hex Compact Impact Driver Kit

2656-22CT (2656-20 Tool-Only)

Specifications:

Fastening Torque	1,500 in-lbs
IPM	0 – 3,450
RPM	0 – 2,750
Chuck Type	1/4" Hex Quick Change
Length	5-1/2"
Weight	3.8 lbs

Includes: 2657-22 (2) M18™ REDLITHIUM™ Compact Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case



M18™ 1/4" 2-Speed Impact Driver Kit

2657-22, 2657-22CT (2657-20 Tool-Only)

Specifications:

Fastening Torque	1,500 in-lbs
IPM	0 – 3,450
RPM	0 – 2,750
Chuck Type	1/4" Hex Quick Change
Length	5-1/2"
Weight	3.8 lbs

Includes: 2657-22 (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case; 2657-22CT Includes (2) M18™ REDLITHIUM™ Compact Battery Packs



M18 FUEL
3/8" Impact Wrench w/ Friction Ring w/ ONE-KEY™ Kit

2758-22, 2758-22CT (2758-20 Tool-Only)

Specifications:

Fastening Torque	210 ft-lbs
IPM	0 – 3,200
RPM	0 – 2,500
DRIVE CONTROL™	4-Mode (Customizable)
Chuck Type	3/8" Friction Ring
Length	5-9/10"
Weight	4.2 lbs

Includes: 2758-22 (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case; 2758-22CT Includes (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs



M18 FUEL
3/8" Compact Impact Wrench w/ Friction Ring Kit

2754-22, 2754-22CT (2754-20 Tool-Only)

Specifications:

Fastening Torque	210 ft-lbs
IPM	0 – 3,200
RPM	0 – 2,500
DRIVE CONTROL™	4-Mode
Chuck Type	3/8" Friction Ring
Length	5-9/10"
Weight	4.2 lbs

Includes: 2754-22 (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case; 2754-22CT Includes (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs



M18™ 3/8" Compact Impact Wrench Kit

2658-22, 2658-22CT (2658-20 Tool-Only)

Specifications:

Fastening Torque	167 ft-lbs
IPM	0 – 3,350
RPM	0 – 2,450
Anvil	3/8" Friction Ring
Length	6"
Weight	4.1 lbs

Includes: 2658-22 (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case; 2658-22CT Includes (2) M18™ REDLITHIUM™ Compact Battery Packs



M18 FUEL
1/2" Compact Impact Wrench w/ Pin Detent w/ ONE-KEY™ Kit

2759-22, 2759B-22 (2759-20, 2759B-20 Tool-Only)

Specifications:

Fastening Torque	220 ft-lbs
IPM	0 – 3,200
RPM	0 – 2,500
DRIVE CONTROL™	4-Mode (Customizable)
Chuck Type	1/2" Pin Detent
Length	6-1/10"
Weight	4.2 lbs

Includes: 2759-22 (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case; 2759B-22 1/2" Compact Impact Wrench w/ Friction Ring w/ ONE-KEY™ Kit



M18 FUEL
1/2" Compact Impact Wrench w/ Pin Detent Kit

2755-22, 2755B-22 (2755-20, 2755B-20 Tool-Only)

Specifications:

Fastening Torque	220 ft-lbs
IPM	0 – 3,200
RPM	0 – 2,500
DRIVE CONTROL™	4-Mode
Chuck Type	1/2" Pin Detent
Length	6-1/10"
Weight	4.2 lbs

Includes: 2755-22 (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case; 2755B-22 1/2" Compact Impact Wrench w/ Friction Ring Kit

