

| PRODUCT DESCRIPTION   | PART NO. | CATEGORY  | LIST PRICE<br>CAD / UNIT |
|---|----------|-----------|--------------------------|
| <b>F2725</b><br>Nuheat standard mat, 120 V, 108"x96", 7.2 Amps, 864 W. Mat<br>dimensions 9' x 8'<br>Weight: 8.8 lbs UPC: 620713000533     | FG0054   | <b>FI</b> | <b>765.44/PC</b>         |
| <b>F2727</b><br>Nuheat standard mat, 120 V, 108"x108", 8.1 Amps, 972 W. Mat<br>dimensions 9' x 9'<br>Weight: 9.4 lbs UPC: 620713000540    | FG0055   | <b>FI</b> | <b>838.58/PC</b>         |
| <b>F3006</b><br>Nuheat standard mat, 120 V, 118"x24", 2.0 Amps, 236 W. Mat<br>dimensions 10' x 2'<br>Weight: 3.2 lbs UPC: 620713000557    | FG0056   | <b>FI</b> | <b>333.78/PC</b>         |
| <b>F3008</b><br>Nuheat standard mat, 120 V, 118"x30", 2.5 Amps, 295 W. Mat<br>dimensions 10' x 2.5'<br>Weight: 3.45 lbs UPC: 620713000564 | FG0057   | <b>FI</b> | <b>386.33/PC</b>         |
| <b>F3009</b><br>Nuheat standard mat, 120 V, 118"x36", 3.0 Amps, 354 W. Mat<br>dimensions 10' x 3'<br>Weight: 3.8 lbs UPC: 620713000571    | FG0058   | <b>FI</b> | <b>429.59/PC</b>         |
| <b>F3010</b><br>Nuheat standard mat, 120 V, 118"x42", 3.4 Amps, 413 W. Mat<br>dimensions 10' x 3.5'<br>Weight: 4.35 lbs UPC: 620713000588 | FG0059   | <b>FI</b> | <b>452.26/PC</b>         |
| <b>F3012</b><br>Nuheat standard mat, 120 V, 118"x48", 3.9 Amps, 472 W. Mat<br>dimensions 10' x 4'<br>Weight: 5.3 lbs UPC: 620713000595    | FG0060   | <b>FI</b> | <b>499.65/PC</b>         |
| <b>F3015</b><br>Nuheat standard mat, 120 V, 118"x60", 4.9 Amps, 590 W. Mat<br>dimensions 10' x 5'<br>Weight: 6.15 lbs UPC: 620713000601   | FG0061   | <b>FI</b> | <b>588.24/PC</b>         |

| PRODUCT DESCRIPTION  | PART NO. | CATEGORY   | LIST PRICE<br>CAD / UNIT              |
|--|----------|------------|---------------------------------------|
| <b>F3018</b><br>Nuheat standard mat, 120 V, 118"x72", 5.9 Amps, 708 W. Mat dimensions 10' x 6'<br>Weight: 7.1 lbs UPC: 620713000618                            | FG0062   | <b>FI</b>  | <b>690.23/PC</b>                      |
| <b>F3021</b><br>Nuheat standard mat, 120 V, 118"x84", 6.9 Amps, 826 W. Mat dimensions 10' x 7'<br>Weight: 8.35 lbs UPC: 620713000625                           | FG0063   | <b>FI</b>  | <b>747.93/PC</b>                      |
| <b>F3025</b><br>Nuheat standard mat, 120 V, 118"x96", 7.9 Amps, 944 W. Mat dimensions 10' x 8'<br>Weight: 9.45 lbs UPC: 620713000632                           | FG0064   | <b>FI</b>  | <b>824.16/PC</b>                      |
| <b>F3027</b><br>Nuheat standard mat, 120 V, 118"x108", 8.9 Amps, 1062 W. Mat dimensions 10' x 9'<br>Weight: 10.3 lbs UPC: 620713000649                         | FG0065   | <b>FI</b>  | <b>908.64/PC</b>                      |
| <b>F3030</b><br>Nuheat standard mat, 120 V, 118"x116", 9.5 Amps, 1141 W. Mat dimensions 10' x 10'<br>Weight: 11.2 lbs UPC: 620713000656                        | FG0066   | <b>FI</b>  | <b>972.51/PC</b>                      |
| <b>F032032-S</b><br>Nuheat shower mat, 120 V, 32"x32" with 5-inch center drain hole, 0.7 Amps; Mat dimensions 2'8" x 2'8"<br>Weight: 2.5 lbs UPC: 620713001509 | FG0307   | <b>FI</b>  | <b>205.01/PC</b>                      |
| <b>STDXLD</b><br>Nuheat standard mat plus extended lead length to 22 ft max (standard is 10 ft)  |          | <b>MTO</b> | <b>Mat Price above plus \$8.24/ft</b> |
| <b>NUHEAT STANDARD MATS, 240 V</b>   |          |            |                                       |
| <b>G1509</b><br>Nuheat standard mat, 240 V, 60"x36", 0.8 Amps, 180 W. Mat dimensions 5' x 3'<br>Weight: 2.8 lbs UPC: 620713000663                              | FG0101   | <b>FI</b>  | <b>284.34/PC</b>                      |



| PRODUCT DESCRIPTION  | PART NO. | CATEGORY  | LIST PRICE<br>CAD / UNIT |
|--|----------|-----------|--------------------------|
| <b>G1510</b><br>Nuheat standard mat, 240 V, 60"x42", 0.9 Amps, 210 W. Mat<br>dimensions 5' x 3.5'<br>Weight: 2.65 lbs    UPC: 620713000670 | FG0102   | <b>FI</b> | <b>307.00/PC</b>         |
| <b>G1512</b><br>Nuheat standard mat, 240 V, 60"x48", 1.0 Amps, 240 W. Mat<br>dimensions 5' x 4'<br>Weight: 3.55 lbs    UPC: 620713000687   | FG0103   | <b>FI</b> | <b>338.94/PC</b>         |
| <b>G1515</b><br>Nuheat standard mat, 240 V, 60"x60", 1.3 Amps, 300 W. Mat<br>dimensions 5' x 5'<br>Weight: 3.95 lbs    UPC: 620713000694   | FG0104   | <b>FI</b> | <b>392.51/PC</b>         |
| <b>G1808</b><br>Nuheat standard mat, 240 V, 72"x30", 0.8 Amps, 180 W. Mat<br>dimensions 6' x 2.5'<br>Weight: 2.8 lbs    UPC: 620713000700  | FG0105   | <b>FI</b> | <b>284.34/PC</b>         |
| <b>G1809</b><br>Nuheat standard mat, 240 V, 72"x36", 0.9 Amps, 216 W. Mat<br>dimensions 6' x 3'<br>Weight: 2.85 lbs    UPC: 620713000717   | FG0106   | <b>FI</b> | <b>318.33/PC</b>         |
| <b>G1810</b><br>Nuheat standard mat, 240 V, 72"x42", 1.1 Amps, 252 W. Mat<br>dimensions 6' x 3.5'<br>Weight: 3.35 lbs    UPC: 620713000724 | FG0107   | <b>FI</b> | <b>354.39/PC</b>         |
| <b>G1812</b><br>Nuheat standard mat, 240 V, 72"x48", 1.2 Amps, 288 W. Mat<br>dimensions 6' x 4'<br>Weight: 3.85 lbs    UPC: 620713000731   | FG0108   | <b>FI</b> | <b>382.20/PC</b>         |
| <b>G1815</b><br>Nuheat standard mat, 240 V, 72"x60", 1.5 Amps, 360 W. Mat<br>dimensions 6' x 5'<br>Weight: 4.25 lbs    UPC: 620713000748   | FG0109   | <b>FI</b> | <b>435.77/PC</b>         |