

PRODUCT DESCRIPTION	PART NO.	CATEGORY	LIST PRICE CAD / UNIT
<b>G2521</b> Nuheat standard mat, 240 V, 96"x84", 2.8 Amps, 672 W. Mat dimensions 8' x 7' Weight: 5.9 lbs    UPC: 620713000977	FG0132	<b>FI</b>	<b>667.57/PC</b>
<b>G2525</b> Nuheat standard mat, 240 V, 96"x96", 3.2 Amps, 768 W. Mat dimensions 8' x 8' Weight: 7.62 lbs    UPC: 620713000984	FG0133	<b>FI</b>	<b>715.99/PC</b>
<b>G2706</b> Nuheat standard mat, 240 V, 108"x24", 0.9 Amps, 216 W. Mat dimensions 9' x 2' Weight: 3.3 lbs    UPC: 620713000991	FG0134	<b>FI</b>	<b>318.33/PC</b>
<b>G2708</b> Nuheat standard mat, 240 V, 108"x30", 1.1 Amps, 270 W. Mat dimensions 9' x 2.5' Weight: 3.05 lbs    UPC: 620713001004	FG0135	<b>FI</b>	<b>361.60/PC</b>
<b>G2709</b> Nuheat standard mat, 240 V, 108"x36", 1.4 Amps, 324 W. Mat dimensions 9' x 3' Weight: 3.7 lbs    UPC: 620713001011	FG0136	<b>FI</b>	<b>406.93/PC</b>
<b>G2710</b> Nuheat standard mat, 240 V, 108"x42", 1.6 Amps, 378 W. Mat dimensions 9' x 3.5' Weight: 4.25 lbs    UPC: 620713001028	FG0137	<b>FI</b>	<b>435.77/PC</b>
<b>G2712</b> Nuheat standard mat, 240 V, 108"x48", 1.8 Amps, 432 W. Mat dimensions 9' x 4' Weight: 5.25 lbs    UPC: 620713001035	FG0138	<b>FI</b>	<b>466.68/PC</b>
<b>G2715</b> Nuheat standard mat, 240 V, 108"x60", 2.3 Amps, 540 W. Mat dimensions 9' x 5' Weight: 6 lbs    UPC: 620713001042	FG0139	<b>FI</b>	<b>557.34/PC</b>

PRODUCT DESCRIPTION	PART NO.	CATEGORY	LIST PRICE CAD / UNIT
<b>G2718</b> Nuheat standard mat, 240 V, 108"x72", 2.7 Amps, 648 W. Mat dimensions 9' x 6' Weight: 6.2 lbs    UPC: 620713001059	FG0140	<b>FI</b>	<b>644.91/PC</b>
<b>G2721</b> Nuheat standard mat, 240 V, 108"x84", 3.2 Amps, 756 W. Mat dimensions 9' x 7' Weight: 7.25 lbs    UPC: 620713001066	FG0141	<b>FI</b>	<b>706.72/PC</b>
<b>G2725</b> Nuheat standard mat, 240 V, 108"x96", 3.6 Amps, 864 W. Mat dimensions 9' x 8' Weight: 7.8 lbs    UPC: 620713001073	FG0142	<b>FI</b>	<b>765.44/PC</b>
<b>G2727</b> Nuheat standard mat, 240 V, 108"x108", 4.1 Amps, 972 W. Mat dimensions 9' x 9' Weight: 9.3 lbs    UPC: 620713001080	FG0143	<b>FI</b>	<b>838.58/PC</b>
<b>G3006</b> Nuheat standard mat, 240 V, 118"x24", 1.0 Amps, 236 W. Mat dimensions 10' x 2' Weight: 3.25 lbs    UPC: 620713001097	FG0144	<b>FI</b>	<b>333.78/PC</b>
<b>G3008</b> Nuheat standard mat, 240 V, 118"x30", 1.2 Amps, 295 W. Mat dimensions 10' x 2.5' Weight: 3.85 lbs    UPC: 620713001103	FG0145	<b>FI</b>	<b>386.33/PC</b>
<b>G3009</b> Nuheat standard mat, 240 V, 118"x36", 1.5 Amps, 354 W. Mat dimensions 10' x 3' Weight: 3.8 lbs    UPC: 620713001110	FG0146	<b>FI</b>	<b>429.59/PC</b>
<b>G3010</b> Nuheat standard mat, 240 V, 118"x42", 1.7 Amps, 413 W. Mat dimensions 10' x 3.5' Weight: 4.5 lbs    UPC: 620713001127	FG0147	<b>FI</b>	<b>452.26/PC</b>

PRODUCT DESCRIPTION	PART NO.	CATEGORY	LIST PRICE CAD / UNIT
<b>G3012</b> Nuheat standard mat, 240 V, 118"x48", 2.0 Amps, 472 W. Mat dimensions 10' x 4' Weight: 5.3 lbs    UPC: 620713001134	FG0148	<b>FI</b>	<b>499.65/PC</b>
<b>G3015</b> Nuheat standard mat, 240 V, 118"x60", 2.5 Amps, 590 W. Mat dimensions 10' x 5' Weight: 5.9 lbs    UPC: 620713001141	FG0149	<b>FI</b>	<b>588.24/PC</b>
<b>G3018</b> Nuheat standard mat, 240 V, 118"x72", 3.0 Amps, 708 W. Mat dimensions 10' x 6' Weight: 7.45 lbs    UPC: 620713001158	FG0150	<b>FI</b>	<b>690.23/PC</b>
<b>G3021</b> Nuheat standard mat, 240 V, 118"x84", 3.4 Amps, 826 W. Mat dimensions 10' x 7' Weight: 8.3 lbs    UPC: 620713001165	FG0151	<b>FI</b>	<b>747.93/PC</b>
<b>G3025</b> Nuheat standard mat, 240 V, 118"x96", 3.9 Amps, 944 W. Mat dimensions 10' x 8' Weight: 8.65 lbs    UPC: 620713001172	FG0152	<b>FI</b>	<b>824.16/PC</b>
<b>G3027</b> Nuheat standard mat, 240 V, 118"x108", 4.4 Amps, 1062 W. Mat dimensions 10' x 9' Weight: 10.6 lbs    UPC: 620713001189	FG0153	<b>FI</b>	<b>908.64/PC</b>
<b>G3030</b> Nuheat standard mat, 240 V, 118"x116", 4.8 Amps, 1141 W. Mat dimensions 10' x 10' Weight: 10.7 lbs    UPC: 620713001196	FG0154	<b>FI</b>	<b>972.51/PC</b>
<b>G144036</b> Nuheat standard mat, 240 V, 144"x36", 1.8 Amps, 432 W. Mat dimensions 12' x 3' Weight: 5 lbs    UPC: 620713010013	FG0422	<b>FI</b>	<b>538.79/PC</b>