

# RAZOR

## ULTRA THIN RECESSED DOWNLIGHT **LED**

The first model in the collection, this traditional style provides numerous design functions. Whether a home or commercial application, its superior brightness and low power usage offer the ideal lighting solution.

### SIZE & MODELS

**3"**

450 lumens

RZR-300-6W-3K-WH  
RZR-300-6W-3K-BLK  
RZR-300-6W-3K-SC  
RZR-300-6W-4K-WH  
RZR-300-6W-4K-BLK  
RZR-300-6W-4K-SC

**4"**

600 lumens

RZR-400-9W-27K-WH  
RZR-400-9W-3K-WH  
RZR-400-9W-3K-BLK  
RZR-400-9W-3K-SC  
RZR-400-9W-4K-WH  
RZR-400-9W-4K-BLK  
RZR-400-9W-4K-SC

**5"**

780 lumens

RZR-500-11W-3K-WH  
RZR-500-11W-3K-BLK  
RZR-500-11W-3K-SC  
RZR-500-11W-4K-WH  
RZR-500-11W-4K-BLK  
RZR-500-11W-4K-SC

**6"**

950 lumens

RZR-600-12W-27K-WH  
RZR-600-12W-3K-WH  
RZR-600-12W-3K-BLK  
RZR-600-12W-3K-SC  
RZR-600-12W-4K-WH  
RZR-600-12W-4K-BLK  
RZR-600-12W-4K-SC



### COLOR TEMPERATURE

**2,700 K**

**3,000 K**

**4,000 K**

### FINISH



WHITE



BLACK



SATIN CHROME



# RAZOR-R

## LED LOW PROFILE REGRESSED RECESSED DOWNLIGHT



The Razor-R series takes illumination to the next level, featuring a design and look that create a wash of light to flow throughout, with minimal hot spots on the ceiling. **This improved Razor-R provides higher performance resulting in greater lumen output, while increasing the lumen per watt efficiency.**

### SIZE & MODELS

4"

750 lumens

RZR-411-9W-3K-WH  
RZR-411-9W-3K-BLK  
RZR-411-9W-3K-SC  
RZR-411-9W-4K-WH  
RZR-411-9W-4K-BLK  
RZR-411-9W-4K-SC

6"

1100 lumens

RZR-611-12W-3K-WH  
RZR-611-12W-3K-BLK  
RZR-611-12W-3K-SC  
RZR-611-12W-4K-WH  
RZR-611-12W-4K-BLK  
RZR-611-12W-4K-SC

### FINISH



SATIN CHROME



BLACK



WHITE

### COLOR TEMPERATURE

3,000 K

4,000 K

