

N253EA8/N253EA8BK

4K Ultra HD WDR Fixed Audio Dome



N253EA8/N253EA8BK 4K Ultra HD WDR Fixed Audio Dome

The FLIR 4K Ultra HD WDR Fixed Audio Dome IP Camera offers exceptional performance and an incredible level of detail in recordings. True WDR capability up to 100dB ensures excellent image quality around the clock, and H.265 delivers improved compression efficiency for significant hard drive space savings. The camera also features a built-in microphone for listen-in audio.

4K HD PICTURE QUALITY

4K Ultra HD (8MP 3840x2160) resolution provides the highest standard in image clarity and detail for evidence collection

- Ultra HD 4K (8MP) @ 15fps, 4MP @ 25fps / 3MP/1080p/720p @ up to 25/30fps
- 2.8mm lens provides a wide angle 112° field of view
- IR night vision range up to 82ft/25m

ADVANCED FEATURES

H.265 compression coupled with Region of Interest (ROI) optimizes video performance based on available bandwidth

- Advanced H.265 & Super H.264[™] compression technology
- Built-in microphone for audio recording*
- 4-Zone Region of Interest

WEATHERPROOF

Installation in any outdoor conditions

- IP67 weatherproof
- -22°F/-30°C Cold Climate capable
- Tamper Detection
- 12V/PoE (802.3af)






^{*} Audio is disabled by default. Audio recording or use of listen-in audio without consent is illegal in certain jurisdictions. FLIR Systems, Inc. does not assume liability for any use of its products that fails to conform with local laws.


Specifications

Camera	N253EA8/N253EA8BK
Imaging Device	Ultra HD 4K (8MP), 1/2.5"
Effective Pixels	3840(H) × 2160(V)
Image Type	CMOS
Image Readout	Progressive Scan
Day / Night	Auto (ICR) / Color / B/W
Mechanical IR Cut Filter	Yes
Min. Illumination	0.2lux @ F1.4 (Color)
	0 lux @ F1.4 (B/W)
S/N Ratio Field of View (H)	≥50dB 112°
IR Illumination	82ft/25m, 850nm
IR On / Off Control	Yes
Video Output	RJ45
Electronic Shutter Range	1/3(4)s - 1/100,000s
Optical	
Lens Type	Fixed
Mount Type	Board Type
Iris Type Iris Control Type	Fixed Auto
Focal Length	2.8mm
Aperture	F1.8
Optical Zoom	N/A
Focus	Fixed
Video	
Video Compression	H.265 / Super H.264™ / MJPEG
Video Streams	H.265 / H.264 / MJPEG Triple Stream
	4K (3840×2160) / 6.3MP (3072×2048) / 5.3MP (3072×1728)
Resolution Selection	/5MP (2592x1944) / 4MP (2688×1520) / 3.7MP
	(2560x1440) / 3MP (2304x1296) / 1080p (1920×1080) / SXGA (1280x1024) / 1.3MP (1280x960) / 720p (1280×720)
Aspect Ratio	16:9 / 4:3 (select non 4K resolutions)
•	Ultra HD 4K (8MP) @ 15fps, 4MP @ 25fps /
Frame rates (Maximum)	3MP/1080p/720p @ up to 25/30fps
Bit Rate Control	CBR/VBR
Bit Rate Selection	H.265: 768 ~ 6912Kbps
	H.264: 2304 ~ 10240Kbps
Quality Setting Range	1-6 (4)
(default)	(1)
Region of Interest (selectable areas)	Yes (4)
Wide Dynamic Range	True WDR
Dynamic Range	100dB
Backlight Compensation	BLC/HLC
White Balance	Auto / Manual
Gain Control	Auto / Manual
Noise Reduction	3D Advanced
Smart IR	Yes, User adjustable
Digital Zoom	Up to 16× Yes
Tamper Detection Video Mirroring/Rotation	Horizontal Mirror / Vertical Flip
Video Overlay	Time / Date / Camera / Custom Text
Window Blanking	
(Privacy)	Up to 4 Areas
Menu Languages	English
Network	
D	IPv4/IPv6, HTTP, HTTPS, SSL, TCP/IP, UDP, UPnP,
Protocols	ICMP, IGMP, SNMP, RTSP, RTP, SMTP, NTP, DHCP,
ONIVIE Conformance	DNS, PPPOE, DDNS, FTP, IP Filter, QoS, Bonjour ONVIF Profile S
ONVIF Conformance	Standard RFC2326 / Supports QuickTime / VLC Player /
RTSP Video	User Security Authentication (Enabled/Disabled)
Users	20 Users
Mechanical	
Material	Aluminum Alloy
Product Dimensions	4.2" W × 3.2" D × 4.2 H
(Dia × H)	106mm × 82mm × 106mm
Product Weight	1.05 lbs / 0.47kg
Electrical	
Network Port	RJ45 (10/100 Base-T)
Analog Video Out	N/A
(service only)	· · · · · · · · · · · · · · · · · · ·
Power Input	12V DC / PoE
Power over Ethernet	PoE (802.3af)
Type	
Type Power Consumption	5.4W
Type Power Consumption Current Consumption	5.4W 420mA

Additional Features	
Edge Storage	N/A
Built-in Heater	N/A
Audio I/O	Built-in Microphone
Audio Encoding	G.711a / G.711Mu / AAC / G.726
Alarm I/O	N/A
Environmental	
Storage Temperature	-22°F ~ +140°F / -30°C ~ +60°C
Storage Humidity	Less than 95% RH
Operating Temperature	-22°F ~ +140°F / -30°C ~ +60°C
Operating Humidity	Less than 95% RH
Cold Start Temperature	-22°F / -30°C
Ingress Protection	IP67 Rated
Vandal Resistance	N/A
Certifications	
Certifications	CE / FCC / RoHS



Dimensions



Available Accessories:

For accessory / mount compatibility visit: www.flir.com/security/cameramounts

Ordering Information

N253EA (grey): 8-41430-01950-3 N253EA8BK (black): 8-41430-01951-0

Package Dimensions

6.1" \times 6.1" \times 5.4" / 155mm \times 155mm \times 138mm. Weight: 1.8lb / 0.8kg 6.1" \times 6.1" \times 5.4" / 155mm \times 155mm \times 138mm. Weight: 1.8lb / 0.8kg N253EA8 N253EA8BK

MARKHAM, ONTARIO

FLIR Systems, Inc. 250 Royal Crest Court Markham, ON L3R 3S1 Canada

PH: +1 866.344.4674

www.flirsecurity.com

Imagery for illustration purposes only. Specifications are subject to change without notice. ©2018 FLIR Systems, Inc. All rights reserved. (Created 03/08/18): 118-0373-SEC.

