

SLIM PROFILE ARCHITECTURAL ALUMINUM MOUNTING CHANNEL

PROJECT	TYPE
CATALOG NUMBER	

LED-CHL-SLIM

PRODUCT DESCRIPTION

Extruded slim mount (only 1/4" depth) aluminum channel with snap on semi-frosted diffusion lens that provides a rigid, shallow linear mounting platform for the following GM Lighting LEDTask Flexible LED Linear Ribbons:

For the following L	or the following LEDTask™ Flexible Linear Ribbon Series				
LTR60/300 Series	12VDC High Output - Dry and Wet location				
LTR60/300-SO Series	12VDC Standard Output - Dry and Wet location				
GM100-24 Series	24VDC Standard Output - Dry and Wet location				
LTR30024 Series	24VDC High Output - Dry and Wet location				
SLR Series	12VDC Standard Output - Damp location				
LTR150-RGB Series	12VDC RGB Series - Dry location				
LTR30/150RGB Series	12VDC RGB Series - Wet location				

MOUNTING


Mount into 3/4"W recessed channel using included mounting clips and screws or adhesive (by others).

Flexible LED linear ribbon uses attached 3M mounting tape. Use LED-CHL-D-EC endcaps for a finished look. Ordered separately.

LENS:


Comes with frosted glossy lens.

PLEASE ALLOW THE FOLLOWING VISUAL CLEARANCE TO ALLOW FOR FLEXIBLE RIBBON TO RIBBON CONNECTORS



NOTE: Channels may not accommodate all ribbon to ribbon and ribbon to power supply connections. Please locate connections outside of channel interior.

Accessories		
LED-CHL-SLIM-EC	Solid end caps for LED-CHL-SLIM	
LED-CHL-SLIM-EC-H	End caps with holes for LED-CHL-SLIM	



Model Number	Description	Length	Height	Width	Finish
LED-CHL-SLIM	Shallow recessed architectural aluminum channel	48"	1/4"	11/16"	Brushed Aluminum