

Bolts/Washers



MACHINE BOLTS & WASHERS

CATALOGUE #	DIMENSIONS DIA.	"L"	"T"	STD. PKG.	WT. LB/C	CATALOGUE #	DIMENSIONS DIA.	"L"	"T"	STD. PKG.	WT. LB/C
612M	1/2"	6"	1 1/4"	25	45	1258M	5/8"	12"	6"	50	115
812M	1/2"	8"	4"	50	56	1458M	5/8"	14"	6"	50	130
1012M	1/2"	10"	4"	50	67	1658M	5/8"	16"	6"	50	145
1212M	1/2"	12"	6"	50	76	1858M	5/8"	18"	6"	50	160
658M	5/8"	6"	1 1/2"	50	70	1034M	3/4"	10"	6"	50	150
858M	5/8"	8"	4"	50	86	1234M	3/4"	12"	6"	50	175
1058M	5/8"	10"	6"	50	102	1434M	3/4"	14"	6"	25	200

See Poleline Catalogue for other sizes.

Minimum breaking strength at thread root:

1/2" dia. - 8500 lbs.

5/8" dia. - 13500 lbs.

3/4" dia. - 20000 lbs.



CATALOGUE #	DESCRIPTION	HOLE DIAMETER	STD. PKG	WT.	
	Square Washers				
1822SW-11	2" x 2" x 1/8"	11/16"	200	15	
3622SW-11	2" x 2" x 3/16"	11/16"	200	22	
3624SW-11	2 1/4" x 2 1/4" x 3/16"	11/16"	200	26	
3624SW-13	2 1/4" x 2 1/4" x 3/16"	13/16"	200	26	
1433SW-13	3" x 3" x 1/4"	13/16"	50	63	
1844SW-11	4" x 4" x 1/8"	11/16"	50	60	
3644SW-13	4" x 4" x 3/16"	13/16"	50	82	
1444SW-13	4" x 4" x 1/4"	13/16"	50	110	
	Curved Washers				
3624CW-13	2 1/4" x 2 1/4" x 3/16"	13/16"	100	26	
1433CW-13	3" x 3" x 1/4"	13/16"	50	60	
1434CW-13	3 1/4" x 3 1/4" x 1/4"	13/16"	50	75	
1444CW-13	4" x 4" x 1/4"	13/16"	50	110	
	Other sizes available upon request				
	Round Washers				
100RW	3/8" Bolt Size	7/16"	500	1.6	
114RW	9/16" Bolt Size	1/2"	500	3.0	
138RW	1/2" Bolt Size	9/16"	500	4.2	
134RW	5/8" Bolt Size	11/16"	500	8.4	
200RW	3/4" Bolt Size	13/16"	500	14.0	

POLELINE & GROUNDING