

**M18™ FORCE LOGIC™ 6T Crimper Kit w/ D3 Grooves and Fixed BG Die**

2678-22BG

**Specifications:**

Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes; PFM™
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"



**Includes:** (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 6T Crimping Jaw with Fixed BG Die, Carabiner, AC/DC Wall and Vehicle Charger, Bucket Bag



**M18™ FORCE LOGIC™ 6T Crimper Kit w/ D3 Grooves and Fixed O Die**

2678-22O

**Specifications:**

Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes; PFM™
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"



**Includes:** (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 6T Crimping Jaw with Fixed O Die, Carabiner, AC/DC Wall and Vehicle Charger, Bucket Bag

**M18™ FORCE LOGIC™ 6T Crimper Kit w/ D3 Grooves and Snub Nose**

2678-22

**Specifications:**

Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes; PFM™
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"



**Includes:** (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 6T Snub Nose Crimping Jaw, Carabiner, AC/DC Wall and Vehicle Charger, Bucket Bag

**M18™ FORCE LOGIC™ 6T Crimper Kit w/ Kearney Grooves**

2678-22K

**Specifications:**

Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes; PFM™
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"



**Includes:** (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 6T Kearney Crimping Jaw, Carabiner, AC/DC Wall and Vehicle Charger, Bucket Bag

**M18™ FORCE LOGIC™ 6T Crimper Accessories**

Compatible with 2678-22BG, 2678-22O, 2678-22, 2678-22K

**6T Utility Crimper Jaws**

- 49-16-BGD3 6T Fixed BG Crimping Jaw;
- 49-16-0OD3 6T Fixed O Crimping Jaw;
- 49-16-00D3 6T Snub Nose Crimping Jaw;
- 49-16-KEAR 6T Kearney Crimping Jaw

**W Style Dies**

- 49-16-WBG0 W Style Die: "W-BG";
- 49-16-WO00 W Style Die: "W-O";
- 49-16-WC00 W Style Die: "W-C";
- 49-16-W840 W Style Die: "W-K840";
- 49-16-W161 W Style Die: "W-161";
- 49-16-W162 W Style Die: "W-162";
- 49-16-W163 W Style Die: "W-163";
- 49-16-W165 W Style Die: "W-165";
- 49-16-W166 W Style Die: "W-166";
- 49-16-W243 W Style Die: "W-243";
- 49-16-W247 W Style Die: "W-247";
- 49-16-W249 W Style Die: "W-249";
- 49-16-W164 W Style Die: "W-164";
- 49-16-W237 W Style Die: "W-237";
- 49-16-W239 W Style Die: "W-239"



**M18™ FORCE LOGIC™ 600 MCM Crimper Kit**

2679-22

**Specifications:**

UL Classification	Yes (All 7 Manufacturers)
Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes; PFM™
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"



**Includes:** (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 600 MCM Commercial U Crimping Jaw, Multi-Voltage Charger, Carrying Case

**Related Accessories:**

49-16-U000 600 MCM Crimping Jaw

**Accessory Kits**

- 49-16-KITA #8 AWG – 350 MCM Aluminum U Style Die Kit;
- 49-16-KITC #8 AWG – 600 MCM Copper U Style Die Kit

**Copper U Style Dies**

- 49-16-U008C #8 Copper 12T U Style Die;
- 49-16-U006C #6 Copper 12T U Style Die;
- 49-16-U004C #4 Copper 12T U Style Die;
- 49-16-U002C #2 Copper 12T U Style Die;
- 49-16-U001C #1 Copper 12T U Style Die;
- 49-16-U01AC 1/0 Copper 12T U Style Die;
- 49-16-U02AC 2/0 Copper 12T U Style Die;
- 49-16-U03AC 3/0 Copper 12T U Style Die;
- 49-16-U04AC 4/0 Copper 12T U Style Die;
- 49-16-U250C 250 MCM Copper 12T U Style Die;
- 49-16-U300C 300 MCM Copper 12T U Style Die;
- 49-16-U350C 350 MCM Copper 12T U Style Die;
- 49-16-U400C 400 MCM Copper 12T U Style Die;
- 49-16-U500C 500 MCM Copper 12T U Style Die;
- 49-16-U600C 600 MCM Copper 12T U Style Die

**Aluminum Dual Rated U Style Dies**

- 49-16-U008 #8 Aluminum 12T U Style Die;
- 49-16-U006 #6 Aluminum 12T U Style Die;
- 49-16-U004 #4 Aluminum 12T U Style Die;
- 49-16-U002 #2 Aluminum 12T U Style Die;
- 49-16-U001 #1 Aluminum 12T U Style Die;
- 49-16-U01A 1/0 Aluminum 12T U Style Die;
- 49-16-U02A 2/0 Aluminum 12T U Style Die;
- 49-16-U03A 3/0 Aluminum 12T U Style Die;
- 49-16-U04A 4/0 Aluminum 12T U Style Die;
- 49-16-U250 250 MCM Aluminum 12T U Style Die;
- 49-16-U300 300 MCM Aluminum 12T U Style Die;
- 49-16-U350 350 MCM Aluminum 12T U Style Die;
- 49-16-U400 400 MCM Aluminum 12T U Style Die;
- 49-16-U500 500 MCM Aluminum 12T U Style Die;
- 49-16-U600 600 MCM Aluminum 12T U Style Die

**M18™ FORCE LOGIC™ 12T Utility Crimper Kit**

2778-22

**Specifications:**

Output Force	12 Tons
Head Rotation	350°
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Length	16"
Weight	11.9 lbs



**Includes:** (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, AC/DC Wall and Vehicle Charger, Carabiner, Utility Bag

**M18™ FORCE LOGIC™ 750 MCM Crimper Kit**

2779-22

**Specifications:**

Output Force	12 Tons
Head Rotation	350°
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Length	16"
Weight	11.5 lbs



**Includes:** (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, Multi-Voltage Charger, Carrying Case

**Related Accessories:**

**Accessory Kits**

- 49-12-KITC EXACT™ #6 AWG – 750 MCM Cu 12T U Style Die Kit;
- 49-12-KITA EXACT™ #6 AWG – 750 MCM Al 12T U Style Die Kit

**EXACT™ 12T Copper U Style Dies**

- 49-12-U008C #8 Copper 12T U Style Die;
- 49-12-U006C #6 Copper 12T U Style Die;
- 49-12-U004C #4 Copper 12T U Style Die;
- 49-12-U002C #2 Copper 12T U Style Die;
- 49-12-U001C #1 Copper 12T U Style Die;
- 49-12-U01AC 1/0 Copper 12T U Style Die;
- 49-12-U02AC 2/0 Copper 12T U Style Die;
- 49-12-U03AC 3/0 Copper 12T U Style Die;
- 49-12-U04AC 4/0 Copper 12T U Style Die;
- 49-12-U250C 250 MCM Copper 12T U Style Die;
- 49-12-U300C 300 MCM Copper 12T U Style Die;
- 49-12-U350C 350 MCM Copper 12T U Style Die;
- 49-12-U400C 400 MCM Copper 12T U Style Die;
- 49-12-U500C 500 MCM Copper 12T U Style Die;
- 49-12-U600C 600 MCM Copper 12T U Style Die;
- 49-12-U750C 750 MCM Copper 12T U Style Die

**EXACT™ 12T Aluminum U Style Dies**

- 49-12-U008 #8 Aluminum 12T U Style Die;
- 49-12-U006 #6 Aluminum 12T U Style Die;
- 49-12-U004 #4 Aluminum 12T U Style Die;
- 49-12-U002 #2 Aluminum 12T U Style Die;
- 49-12-U001 #1 Aluminum 12T U Style Die;
- 49-12-U01A 1/0 Aluminum 12T U Style Die;
- 49-12-U02A 2/0 Aluminum 12T U Style Die;
- 49-12-U03A 3/0 Aluminum 12T U Style Die;
- 49-12-U04A 4/0 Aluminum 12T U Style Die;
- 49-12-U250 250 MCM Aluminum 12T U Style Die;
- 49-12-U300 300 MCM Aluminum 12T U Style Die;
- 49-12-U350 350 MCM Aluminum 12T U Style Die;
- 49-12-U400 400 MCM Aluminum 12T U Style Die;
- 49-12-U500 500 MCM Aluminum 12T U Style Die;
- 49-12-U600 600 MCM Aluminum 12T U Style Die;
- 49-12-U750 750 MCM Aluminum 12T U Style Die

