

Project Name

Location

Prepared By



SATCO S11814

14.5WLED/CDL/4/ADJ-CCT/40D

Notes

[www] 01-29-2021 11:42:01

General

Status	Active
Recessed Can Size	4 in.
Wattage	8.5W/11W/14.5W
Voltage	120V-277V
Finish	Silver
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Lumen Output	600L / 800L / 1020L
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
CRI	80
Beam Angle	40
Rated Hours	50000
Operating Temperature	-20C (-4F) to a maximum of +40C (104F)
Dimmable	0-10V Dimming Only
IC Rated	Yes

Dimensions

Width (in.)	4.65
Height (in.)	2.69
Weight (lb.)	1.23

Compliance

Safety Listing	cETLus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2353229
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Additional Information	Adjustable color temperature (CCT) 2700K 3000K 3500K 4000K 5000K. Three lumen ranges 600L/800L/1020L
Warranty	5 Year Limited - LED Commercial Downlights