


# Narrow slot wiring duct

A

## Designed to fit the spacing of high-density terminal blocks.

### Narrow slot wiring duct — PVC




- Higher number of smaller fingers for more concise harnessing
- Non-slip cover does not slide easily and resists vibration
- Rounded edges protect hands and wires
- V-shaped slot lead-in enables easier and faster wire installation
- Restricted slot design makes sure that wires are held with or without the cover inserted
- Cover attaches flush with sidewall for finished look
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct
- Finger design restricts wire from slipping along the edge; creates two or three levels of wire service (see page B-6 for illustration)
- Integrated mounting holes — larger sizes include staggered holes for mounting flexibility (see page B-6 for illustration)
- Constructed of flame-retardant PVC
- Lead-free construction




For a complete listing of narrow slot dimensional details, see page B-6.



A



Bottom view



Side view

Cat. no.	Description (in.)	Size (W x H)		Cover cat. no.	Duct std. ctn. qty.	Cover std. ctn. qty.	Length (ft.)
		In.	mm				
TYD75X15NP[ _ ]6	0.75 x 1.5 Narrow slot duct	0.94 x 1.60	23.9 x 39.6	TYD75CP[ _ ]6	120	120	6
TYD1X1NP[ _ ]6	1 x 1 Narrow slot duct	1.25 x 1.14	31.8 x 27.7	TYD1CP[ _ ]6	120	120	6
TYD1X15NP[ _ ]6	1 x 1.5 Narrow slot duct	1.25 x 1.60	31.8 x 39.9	TYD15CP[ _ ]6	60	120	6
TYD1X2NP[ _ ]6	1 x 2 Narrow slot duct	1.25 x 2.10	31.8 x 52.8				
TYD1X3NP[ _ ]6	1 x 3 Narrow slot duct	1.25 x 3.05	31.8 x 77.7				
TYD1X4NP[ _ ]6	1 x 4 Narrow slot duct	1.25 x 4.37	31.8 x 111.3				
TYD15X1NP[ _ ]6	1.5 x 1 Narrow slot duct	1.75 x 1.14	44.5 x 27.7	TYD2CP[ _ ]6	120	120	6
TYD15X15NP[ _ ]6	1.5 x 1.5 Narrow slot duct	1.75 x 1.60	44.5 x 39.9				
TYD15X2NP[ _ ]6	1.5 x 2 Narrow slot duct	1.75 x 2.10	44.5 x 52.8				
TYD15X3NP[ _ ]6	1.5 x 3 Narrow slot duct	1.75 x 3.05	44.5 x 77.7				
TYD15X4NP[ _ ]6	1.5 x 4 Narrow slot duct	1.75 x 4.37	44.5 x 111.3	TYD25CP[ _ ]6	60	120	6
TYD2X1NP[ _ ]6	2 x 1 Narrow slot duct	2.25 x 1.24	57.2 x 28.4				
TYD2X15NP[ _ ]6	2 x 1.5 Narrow slot duct	2.25 x 1.70	57.2 x 40.4				
TYD2X2NP[ _ ]6	2 x 2 Narrow slot duct	2.25 x 2.19	57.2 x 53.3				
TYD2X3NP[ _ ]6	2 x 3 Narrow slot duct	2.25 x 3.14	57.2 x 78.2	TYD3CP[ _ ]6	60	120	6
TYD2X4NP[ _ ]6	2 x 4 Narrow slot duct	2.25 x 4.46	57.2 x 111.8				
TYD2X5NP[ _ ]6	2 x 5 Narrow slot duct	2.25 x 5.15	57.2 x 129.3				
TYD25X2NP[ _ ]6	2.5 x 2 Narrow slot duct	2.75 x 2.19	69.9 x 53.6				
TYD25X3NP[ _ ]6	2.5 x 3 Narrow slot duct	2.75 x 3.14	69.9 x 78.2	TYD4CP[ _ ]6	120	120	6
TYD25X4NP[ _ ]6	2.5 x 4 Narrow slot duct	2.75 x 4.46	69.9 x 111.8				
TYD3X1NP[ _ ]6	3 x 1 Narrow slot duct	3.25 x 1.24	82.6 x 29.0				
TYD3X2NP[ _ ]6	3 x 2 Narrow slot duct	3.25 x 2.19	82.6 x 54.9				
TYD3X3NP[ _ ]6	3 x 3 Narrow slot duct	3.25 x 3.14	82.6 x 79.8	TYD4X5NP[ _ ]6	30	60	6
TYD3X4NP[ _ ]6	3 x 4 Narrow slot duct	3.25 x 4.46	82.6 x 113.5				
TYD3X5NP[ _ ]6	3 x 5 Narrow slot duct	3.25 x 5.15	82.6 x 130.6				
TYD4X2NP[ _ ]6	4 x 2 Narrow slot duct	4.25 x 2.19	108.0 x 55.1				
TYD4X3NP[ _ ]6	4 x 3 Narrow slot duct	4.25 x 3.14	108.0 x 80.0				
TYD4X4NP[ _ ]6	4 x 4 Narrow slot duct	4.25 x 4.46	108.0 x 113.8				
TYD4X5NP[ _ ]6	4 x 5 Narrow slot duct	4.25 x 5.15	108.0 x 130.8				

[ ] = space for colour identifier:

- G = Grey
- W = White
- B = Black
- I = Intrinsic blue

- Standard lengths are 6 feet.
- + Catalogue number must be completed by adding suffix G for grey, W for white, I for intrinsic blue, B for black.
- Example: TYD75X15NPG6 is a 0.75" x 1.5" narrow slot grey duct.
- To order duct without mounting holes, add suffix NM to catalogue number.
- Example: TYD75X15NPG6NM is a 0.75" x 1.5" narrow slot grey duct with no mounting holes.
- To order adhesive-backed duct, add suffix A to Catalogue Number.
- Example: TYD75X15NPG6A is a 0.75" x 1.5" narrow slot grey duct with adhesive backing. Shelf life for adhesive is 1 year.
- PVC vinyl duct is CSA certified, UL® Recognized and CE compliant.