



20 AMP NEMA L720 SINGLE RECEPTACLE

L720R | [Pass & Seymour](#)

FEATURES & BENEFITS

Receptacle Single 3wire 20amp 277volt Turnlok



PRODUCT
ENVIRONMENTAL PROFILE

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

SPECIFICATIONS

GENERAL INFO

Type: Single Receptacles
Number Of Wires: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Standard: Yes
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: Yes
UL Listing No: 498
UL Standard: Yes
UN SPSC: 39121403
UR: No

DIMENSIONS

Depth (US): 1.19"

Height (US): 3.28"

Width (US): 1.61"

TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: L720

Volts: 277V

Volts (AC): 277

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

