

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301050058](#)  
**Status:** **Active**  
**Overview:** [Specialty Lighting](#)  
**Description:** Super-Safeway Rubber Hand Lamp, 75W for use with Low Voltage Workstation with Screw Release Guard, Cord Type 14/2 SOOW, 15.24m (50.0') Cord Length

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA E59049  
 UL E59049

**General**

Product Family Portable Lighting  
 Series [130105](#)  
 NEMA Configuration Non-NEMA  
 Outlet None  
 Overview [Specialty Lighting](#)  
 Product Name Super-Safeway  
 Type Hand Lamps, Specialty Light  
 UPC 78678862522

**Physical**

Cord Length - Primary 15.24m (50.0')  
 Cord Length - Secondary N/A  
 Depth 101.60mm (4.000")  
 Duty Industrial  
 Guard Included Yes  
 Guard Type Screw Release  
 Height 374.65mm (14.750")  
 Length N/A  
 Material - Guard N/A  
 Mounting Style Hand Held  
 Packaging Type Carton  
 Socket Construction N/A

**Electrical**

Bulb Type Incandescent  
 Cord Type - Secondary 14/2 SOOW  
 Lamp Type A21  
 Lamp Wattage - Maximum 75W  
 Lumens 1000  
 On/Off Switch No  
 Voltage (Fixture) - Maximum 12V AC  
 Voltage (Secondary) - Maximum 12V AC

**Material Info**

Engineering Number 1648-12



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130105 Series](#)