

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301020234](#)  
**Status:** **Active**  
**Overview:** [Hand Lamps](#)  
**Description:** Super-Safeway Rubber Hand Lamp, PAR 38 Guard, with Switch and Receptacle

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR85374

**General**

Product Family Portable Lighting  
 Series [130102](#)  
 NEMA Configuration N/A  
 Outlet Side  
 Overview [Hand Lamps](#)  
 Product Name Super-Safeway  
 Type Hand Lamps  
 UPC 78678860197

**Physical**

Cord Length - Primary N/A  
 Cord Length - Secondary N/A  
 Depth N/A  
 Duty Industrial  
 Guard Included Yes  
 Guard Type Open End, PAR 38  
 Height 285.50mm (11.240")  
 Length N/A  
 Material - Guard #8 Gauge Zinc-plated Steel  
 Mounting Style Hand Held  
 Packaging Type Carton  
 Socket Construction N/A

**Electrical**

Bulb Type Incandescent  
 Lamp Type PAR38  
 Lamp Wattage - Maximum 100W  
 Lumens 1000  
 On/Off Switch Yes  
 Voltage (Fixture) - Maximum 240V

**Material Info**

Engineering Number 119US



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130102 Series](#)