

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301080136](#)  
**Status:** **Active**  
**Overview:** [Hand Lamps](#)  
**Description:** Super-Safeway 13W Fluorescent Hand Lamp Ballast in Handle with Switch, Cord Type 16/3 SJTOW, Cord Length 15.24m (50.0')

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR85374  
 UL E59049

**General**

Product Family Portable Lighting  
 Series [130108](#)  
 NEMA Configuration NEMA 5-15  
 Outlet None  
 Overview [Hand Lamps](#)  
 Product Name Super-Safeway  
 Type Hand Lamps  
 UPC 78678861287

**Physical**

Cord Length - Primary 15.24m (50.0')  
 Cord Length - Secondary N/A  
 Depth 38.10mm (1.500")  
 Duty Industrial  
 Guard Included No  
 Guard Type N/A  
 Height 66.04mm (2.600")  
 Length 431.80mm (17.000")  
 Material - Globe Butyrate  
 Material - Guard Nitrile Rubber 80 Shore A  
 Mounting Style Hand Held  
 Net Weight 9525.440/g  
 Packaging Type Carton  
 Socket Construction N/A

**Electrical**

Bulb Type Fluorescent  
 Cord Type - Primary 16/3 SJTOW  
 Lamp Type PL13/41  
 Lamp Wattage - Maximum 13W  
 Lumens 900  
 On/Off Switch Yes  
 Voltage (Fixture) - Maximum 120VAC 60 HZ

**Material Info**

Engineering Number 1087-3



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130108 Series](#)