

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301080106](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Super-Safeway 13W Fluorescent Hand Lamp with Switch Cord Ballast Location, Cord Type 18/3 SJTOOW, Cord Length 7.62m (25.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Portable Lighting
Series	130108
NEMA Configuration	NEMA 5-15
Outlet	None
Overview	Hand Lamps
Product Name	Super-Safeway
Type	Hand Lamps
UPC	78678861270

Physical

Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Depth	38.10mm (1.500")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	66.04mm (2.600")
Length	342.90mm (13.500")
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Hand Held
Net Weight	1841.583/g
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Fluorescent
Cord Type - Primary	18/3 SJTOOW
Lamp Type	PL13/41
Lamp Wattage - Maximum	13W
Lumens	900
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info

Engineering Number	1083-3
--------------------	--------



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130108 Series](#)