

# Quality Products. Service Excellence.

# Type 4X Polyester Junction Box PJ Series

Continuous Hinge Door with Twist/Snap Latches

















## **Application**

- Designed for use as instrument enclosures, electric, hydraulic or pneumatic control housings, electrical junction boxes or terminal wiring enclosures.
- Provides outstanding insulation and protection where equipment may be hosed down or be very wet.
- Ideal in applications with high temperatures or highly corrosive environments.

#### **Standards**

- UL 508A Type 1, 2, 3, 4, 4X, 12, & 13
- CSA Type 1, 2, 3, 4, 4X, 12, & 13
- · Complies with
  - o NEMA Type 1, 2, 3, 4, 4X,12, & 13
  - o IEC 60529, IP66

#### Construction

- Molded fiberglass polyester enclosure with matching cover is easily punched, cut, or drilled.
- Enhanced UV inhibitors protect against outdoor weathering.
- 10-32 threaded brass inserts are provided for optional inner panel or terminal kit mounting. Mounting hardware is included.
- Stainless steel butterfly type "twist latch" door fasteners.
- Stainless steel draw type "snap latch" door fasteners.
- · Door fasteners include a provision for padlocking.
- Twist latch enclosures are available with bonded polycarbonate viewing windows.
- Door is supported with a continuous stainless steel hinge.
- · Captive oil resistant gasket provides a positive seal.
- Threaded brass inserts are provided for mounting feet to the rear of the enclosure.
- Stainless steel mounting brackets and hardware are provided for mounting to the rear of the enclosure.
- Operating temperatures between 130°C and -40°C (266°F to -40°F).
- Impact index of 6.78J (5 ft/lb).
- For corrosion resistance information, please refer to table in the Technical Information section.

#### **Finish**

- Fiberglass polyester material has a gray finish.
- Optional inner panels are available in white powder coated finished steel, unfinished aluminum, or Fiberglass.

#### **Accessories**

- Additional Inner Panels
- Pole Mounting Kit
- Window Kits

- Terminal Kit Assemblies
- PJ/PJU/PCJ Replacement Hardware Kits
- PJ Stainless Replacement Mounting Feet

Climate Control

· General Accessories

# New and improved PDF part drawing files with more detail now available.

Click part number in table below to access PDF, DXF, and STEP files.

### **Snap Latch**

	Enclosure			Optional Inner Panel			
Part No.	Н	W	D	Н	W	Part No.	
PJ664L	6.10	6.10	4.18	4.88	4.88	14R0505	
PJ864L	8.00	6.12	4.13	6.75	4.88	14R0705	
PJ1084L	10.13	8.26	4.13	8.75	6.88	14R0907	
PJ1086L	10.13	8.26	6.13	8.75	6.88	14R0907	
PJ12106L	12.13	10.26	6.13	10.75	8.88	14R1109	
PJ12124L	12.13	12.13	4.13	10.75	10.88	14R1111	
PJ12126L	12.13	12.13	6.13	10.75	10.88	14R1111	
PJ14126L	14.13	12.26	6.13	12.75	10.88	14R1311	
PJ16148L	16.27	14.40	8.13	14.75	12.88	14R1513	
PJ18168L	18.40	16.40	8.13	16.88	14.88	P1868	
PJ20168L	20.00	16.00	8.13	18.44	14.44	P2068	

Alternative inner panel options also available.

#### **Twist Latch**

		Enclosure			Optional Inner Panel		
Part No.	Н	W	D	Н	W	Part No.	
PJ664T	6.10	6.10	4.18	4.88	4.88	14R0505	
PJ864T	8.00	6.12	4.13	6.75	4.88	14R0705	
PJ1084T	10.13	8.26	4.13	8.75	6.88	14R0907	
PJ1086T	10.13	8.26	6.13	8.75	6.88	14R0907	
PJ12106T	12.13	10.26	6.13	10.75	8.88	14R1109	
PJ14126T	14.13	12.26	6.13	12.75	10.88	14R1311	
PJ16148T	16.27	14.40	8.13	14.75	12.88	14R1513	
PJ18168T	18.40	16.40	8.13	16.88	14.88	P1868	
PJ20168T	20.00	16.00	8.13	18.44	14.44	P2068	

Alternative inner panel options also available.

Data subject to change without notice

© 2021. Hammond Manufacturing Ltd. All rights reserved.