

## Quality Products. Service Excellence.

## **Vertical Mounting Wall Rack VPB Series**

Heavy Duty 135 lbs (61 kg) Weight Capacity

## **Features:**



- · Constructed in 14-gauge steel.
- 19" mounting EIA tapped 10-32 mounting rails.
- Horizontal or vertical equipment mounting.
- · Rear cable access for cable management.
  - Side cable access included for the 6U rack.
- Finished in smooth black powder paint.
- Includes a package of ten (10) SCREW1032-10 screws.
- Tested to nearly double the suggested load rating of 135 lbs (61 kg).
- TAA Compliant.
- RoHS Compliant.
- · Manufactured in North America.







The VPB196UBK can also be rack mounted to a 2-post rack to provide for vertical rack mounting for deep equipment.









- Universal Rack Shelf
- 10-32 Mounting Screw and Clip Nut Combo-Pack
- Hinged Clear Security Cover
- · PDUs and Outlet Strips





	Overall Dimensions			Rack	<b>Mounting Dimensions</b>	
Part No.	Height	Width	Depth	Units	Height	Width
VPB192UBK	7.69	19.19	4.19	2U	3.50	19.00
VPB194UBK	7.69	19.19	7.69	4U	7.00	19.00
VPB196UBK	11.19	19.19	11.19	6U	10.50	19.00

6U Ships unassembled in a flat-pack.

Tags: Vertical Rack Bracket, Vertical Low Profile, Vertical Rack, Hub-brackets, knock-down, knock down, vp8194ubk, vp8

Data subject to change without notice

© 2021. Hammond Manufacturing Ltd. All rights reserved.