



Quality Products. Service Excellence.

2-Post Open Frame Rack *RB-2P Series*

UL 2416 Rated 1,000 lbs (454 kg) Weight Capacity



Features:

- Constructed in 12-gauge steel.
- 19" EIA compliant 10-32 double-tapped rails.
 - Includes marked rack unit dividers to aid in equipment mounting.
- Don't forget to order your **Mounting Hardware**.
- Side ganging and accessory mounting holes.
- Includes two (2) pairs of integrated 10-32 ground studs, spaced 5/8" apart. Stud pairs are conveniently located across from each other inside the rail channel. For added convenience, a pair is located near the top of the rack, while the other pair is located at the lower side.
- UL Listed 2416 load rated for up to 1,000 lbs (453 kg). Static Load tested to 4,000 lbs (1,814 kg).
- Finished in satin black powder paint.
- Rails and base packaged in cardboard to prevent freight damage.
- TAA compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.

Part of the Rack Basics® line of economy rack solutions.

Gallery



Accessories

- High-Density Vertical Finger Manager with Slam-Latching Door
- Vertical Rack Cable Manager with Door
- Top Wire Management
- Horizontal Finger Cable Manager
- Universal Rack Shelf
- Two Post Mounting Deep Channel Shelf
- Two Post Mounting Keyboard & Equipment Shelf
- 2-Post Rack Low Profile Dolly
- Rack Isolation Kit
- 10-32 Mounting Hardware
- Vertical Finger Cable Manager with Door
- Vertical Cable Manager Extensions
- Horizontal Ring Cable Manager
- Rack Panels
- Two Post Mounting Adjustable Shelf
- Two Post Centered Shelf
- Two-Post Extension Support Bracket
- Open Frame Rack and Rack Cabinet Joining Kit
- Grounding & Bonding
- PDUs and Outlet Strips

Part No.	Overall Dimensions	Rack	Mounting Dimensions	Optional Vertical
----------	--------------------	------	---------------------	-------------------

Part No.	Height Overall	Width	Dimensions Depth	Units	Height	Mounting Dimension	Width	Cable Manager
	Height	Width	Depth	Units	Height	Width		Cable Manager
RB-2P24	48.12	20.46	15.00	24U	42.16	19.00		RB-VCM24
RB-2P77	83.12	20.46	15.00	44U	77.12	19.00		RB-VCM44
RB-2P84	90.12	20.46	15.00	48U	84.16	19.00		RB-VCM48

Tags: **Relay Rack, H-Frame, Server Rack, Equipment Rack, Network Rack, Skeleton Rack, Telco Rack**, *Data subject to change without notice*
Two-Post Rack

© 2021. Hammond Manufacturing Ltd. All rights reserved.