

Quality Products. Service Excellence.

Type 4X Polyester Wallmount Enclosure PJW Series

Continuous Hinge Door with Twist Latches and 3 Pt Handle







Panel Sold Separately









Application

- Designed for use as instrument enclosures, electric, hydraulic or pneumatic control housings, electrical junction boxes or terminal wiring enclosures.
- Provides outstanding insulation and protection where equipment may be hosed down or be very wet.
- Ideal in applications with high temperatures or highly corrosive environments.

Standards

- UL/cUL 508A Type 1, 2, 3, 4, 4X, 12 and 13
- CSA Type 1, 2, 3, 4, 4X, 12 and 13
- · Complies with
 - o NEMA Type 1, 2, 3, 4, 4X,12 and 13
 - o IEC 60529, IP66

Construction

- Molded fiberglass polyester enclosure with matching cover is easily punched, cut, or drilled.
- Enhanced UV inhibitors protect against outdoor weathering.
- 3/8 collar studs are provided for optional inner panel mounting, hardware included. Note:
 Sizes 36x36" and larger have 8 collar studs for added stiffness.
- Stainless steel butterfly type "twist latch" door fasteners with padlock provision.
- · Captive oil resistant gasket provides a positive seal.
- Integrated mounting flange.
- Operating temperatures between 130°C and -40°C (266°F to -40°F).
- Impact index of 6.78J (5 ft/lb).
- For corrosion resistance information, please refer to table in the Technical Information section.

Finish

- Fiberglass polyester material has a gray finish.
- Optional inner panels are available in white powder coated finished steel.

Accessories

- Additional Inner Panels
- Window Kits
- General Accessories

- Pole Mounting Kit
- Climate Control

New and improved PDF part drawing files with more detail now available.

Click part number in table below to access PDF, DXF, and STEP files.

Latch	3 Pt Handle		Enclosure			Optional Inner Panel		
Part No.	Part No.	Н	W	D	Н	W	Part No.	
PJEC363012T	PJEC3630123PT	36.48	30.50	12.18	33.00	27.00	18P3327	
PJEC363012TW	PJEC3630123PTW	36.48	30.50	12.18	33.00	27.00	18P3327	
PJW363014L	PJW363014L3PT	36.25	30.25	14.13	33.00	27.00	18P3327	
PJW363610L	PJW363610L3PT	36.25	36.25	10.13	33.00	33.00	18P3333	
PJW363614L	PJW363614L3PT	36.25	36.25	14.13	33.00	33.00	18P3333	
PJW483610L	PJW483610L3PT	48.25	36.25	10.13	45.00	33.00	18P4533	
PJW483614L	PJW483614L3PT	48.25	36.25	14.13	45.00	33.00	18P4533	
PJW603610L	PJW603610L3PT	60.25	36.25	10.13	57.00	33.00	18P5733	
PJW603614L	PJW603614L3PT	60.25	36.25	14.13	57.00	33.00	18P5733	

Parts ending in W have window. Alternative inner panel options also available.

Data subject to change without notice

© 2021. Hammond Manufacturing Ltd. All rights reserved.