




*Quality Products. Service Excellence.*

## Adjustable Depth Wall Rack with Shelf *APBS Series*

Rugged 100 lbs (45 kg) Weight Capacity

### Features



- Available in 4U and 8U mounting heights.
  - Includes 3.5" (2U) of space for non rack mounting equipment.
- Includes twelve (12) inch depth accessory shelf.
- Adjusts in depth from 12" to 18" with ease so there is no need to disassemble the whole rack to adjust the depth.
- Rear cable access with multiple tie points for cable management.
- Knockdown design ships unassembled for easy handling, reduced freight cost and shipping protection.

### Specifications



- Constructed in 14-gauge steel.
- Tapped 10-32 19" mounting rails are constructed in 14-gauge steel and include rack unit indicators.
  - **SCREW1032-25**, 25-pack of 10-32 mounting hardware included.
- Load rated for up to 100 lbs (45 kg).
- Finished in smooth black powder paint.
- TAA compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.



### Accessories

- Universal Rack Shelf
- Rack Panels
- 10-32 Mounting Hardware
- Cable Managers
- Hook and Loop Roll
- PDUs and Outlet Strips





Part No.	Overall Dimensions		Rack Units	Mounting Dimensions			
	Height	Width		Height	Width	Min Depth	Max Depth
APBS194UBK	10.54	19.25	4U	7.00	19.00	12.00	18.00
APBS198UBK	17.46	19.25	8U	14.00	19.00	12.00	18.00

### What's Inside the Box

Qty Included	Description	Replacement Part No.
1	Rear wall-mounting section	
1	Left side section	
1	Right side section	
2	Sliding Rails	
1	Shelf/Cover	
25	10-32 x 0.75in Rack Mounting Screws	<b>SCREW1032-25</b>
10	10-32 x 3/8 Assembly hardware	
1	Assembly Instructions	

Tags: **Hub-Shelf, Hub Shelf, knock-down, knock down, HA8UWBS, HA4UWBS**

*Data subject to change without notice*

© 2021. Hammond Manufacturing Ltd. All rights reserved.