

CurrentWatch ECS Top Terminal Current Switch

ECSNOASP

UPC:786685120935

Dimensions:

- **Height:** 2.25 IN
- **Length:** 3.53 IN
- **Width:** 1.19 IN

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 0.15A at 240 Vac/dc
- **Contact Configuration:** SSR
- **Enclosure Material:** UL94 V0 flammability rated plastic
- **Input Voltage:** Self powered
- **Led Indicators:** LED indicator
- **Maximum Ac Current:** 150A
- **Operating Temperature:** -58° to 122°F
- **Switch Type:** Adjustable 1.75-150A setpoint

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [CurrentWatch current sensors](#)
- [Eaton Specification Sheet - ECSNOASP](#)

Certifications: No Data

Product compliance: No Data

