



15A, 125V RUBBER DUST-TIGHT PLUG, YELLOW

1447 | [Pass & Seymour](#)

FEATURES & BENEFITS

Straight Blade Rubber Plug 15amp 125volt 5-15p



- Rubber body construction stands up to impacts, oils, chemicals, heat, and weather.
- Floating blades allow self-alignment with contacts for a firm, even electrical connection.
- Terminal screws backed-out, ready-to-wire, saving time and money.
- Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.
- Quick-drive assembly screws allow for fast installation, saving time and money.
- Self-centering cord clamps provide superior strain relief.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Yellow
Number Of Poles: 2
Number Of Wires: 3
Special Features: Rubber, Dust-Tight

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: c22.2 No. 42M
CSA Listed: Yes
CSA Standard: Yes
cULus: No
cURus: No
Federal Spec: No
UL Listing No: UL498

UL Standard: Yes
UN SPSC: 39121402
UR: No

DIMENSIONS

Depth (US): 2.27"
Diameter (US): 1.60"
Height (US): 1.53"
Length (US): 2.44"

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: 5-15
Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

