

---

## 15A, 125V WATERTIGHT CONNECTOR, YELLOW

15W47 | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Rated watertight for 1,500 psi high-pressure hosedown, P&S plugs and connectors feature multiple seals to ensure protection against the environment. Constructed of a sturdy rubber body, which makes them impact- and chemical-resistant, they have nickel-plated blades and contacts for superior corrosion resistance.



- Rubber body construction stands up to impacts, oils, chemicals, heat and weather.
- Floating blades allow self-alignment with contacts for a firm, even electrical connection.
- Terminal screws backed-out, ready-to-wire, saving time and money.
- Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.
- Compression-type cord grip provides watertight seal and 205 lb. pull out strength.
- Multiple ring seals between plug and connector ensures protection from water and contaminants.
- Quick-drive assembly screws allow for fast installation to save time and money.
- NEMA 4, 4X, Watertight. IP65, 66, 67.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Yellow

Type: Connector

Features: Watertight

Number Of Poles: 2 Pole

Number Of Wires: 3 Wire

Special Features: Watertight,NEMA

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes  
UL Listing No: E146159  
UL Standard: Yes  
UN SPSC: 39121402

#### **DIMENSIONS**

Diameter (US): 1.81"  
Length (US): 4.01"

#### **TECHNICAL INFORMATION**

Amps: 15A  
NEMA Configuration Number: 5-15R  
NEMA Rating: 4X/6P  
Volts: 125V

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant

