



## 24W47 WATERTIGHT NEMA 4X/6P LOCKING PLUG

24W47 | [Pass & Seymour](#)

### FEATURES & BENEFITS

Locking Watertight Plug, 15amp 125volt, NEMA Configuration L5-15, multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P & IP67 rated.



- Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather.
- Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.
- Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.
- Devices resist high-pressure hose down of 1,500 psi.
- Color coded sealing bushings provided for large range of cord diameters
- Large ribs on body for a superior grip when mating.

### SPECIFICATIONS

#### GENERAL INFO

Color: Yellow

Type: Plug

Features: Watertight

Number Of Poles: 2

Number Of Wires: 3

Special Features: Watertight, NEMA

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 42M

CSA Standard: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121403

## DIMENSIONS

Diameter (US): 1.63"

Length (US): 2.68"

## TECHNICAL INFORMATION

Amps: 15A

Material: Rubber

NEMA Configuration Number: L5-15

NEMA Rating: 4X/6P

Volts: 125V

Volts (AC): 125

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

