



# EXTRA HEAVY-DUTY SPEC. GRADE 347VAC TOGGLE SWITCH BACK & SIDE WIRE, BROWN

PS371530 | Pass & Seymour

#### **FEATURES & BENEFITS**

Canadian 3way Switch, Back & Side Wire, 15amp 347volt, Brown



- External screw-pressure-plate back and side wired. Accepts #14 #10 AWG copper or copper-clad conductors
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Cam controls fast "make" and positive "break" to minimize arcing.
- Heavy-duty bumper pads for quiet operation.
- High strength thermoplastic polycarbonate toggle.
- · Back body made of glass-reinforced nylon.
- Locking support provides resistance to face and back body separation.
- Oversized silver alloy contacts for long life and better heat dissipation.
- · Grounding terminal is standard.
- Shallow design for ease of installation.
- Strap nickel-plated steel with integral ground.
- · Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

### **SPECIFICATIONS**

## **GENERAL INFO**

Color: Brown Type: Toggle

Duty: Extra Heavy Duty Number Of Poles: 3-way RoHS: Yes

CSA Listing Info: C22.2 111

CSA Standard: Yes UN SPSC: 39121507

## **DIMENSIONS**

Depth (US): 1.073" Height (US): 3.531" Width (US): 1.320"

# TECHNICAL INFORMATION

Amps: 15A Volts: 347VAC Volts (AC): 347

Grade Type: Specification

# **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

