



15 AMP NEMA L615 DUPLEX RECEPTACLE

4550 | [Pass & Seymour](#)

FEATURES & BENEFITS

Receptacle Duplex 15amp 250volt Turnlok - not designed for split circuits



- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

SPECIFICATIONS

GENERAL INFO

Type: Receptacles

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 No. 42, C22.2 No. 230

CSA Standard: Yes

UL Listing No: 498

UL Standard: Yes

UN SPSC: 39121403

DIMENSIONS

Depth (US): 1.150"

Height (US): 2.270"

Width (US): 1.500"

TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: L615

Volts: 250V

Volts (AC): 250

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

