



## HEAVY-DUTY SPEC GRADE SINGLE RECEPTACLES, SIDE WIRE, 15A, 125V, BROWN

5251 | [Pass & Seymour](#)

### FEATURES & BENEFITS

Heavy-Duty Spec Grade Single Receptacle Side, Wire 15amp 125volt, Brown



- Auto-ground clip assures positive ground.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.
- Backed-out tr-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility.
- One-piece brass triple-wire power contacts for lasting retention.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

### SPECIFICATIONS

#### GENERAL INFO

Color: Brown  
Type: Single Receptacles  
Duty: Heavy Duty  
Special Features: Side Wire

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: C22.2 No. 42  
CSA Standard: Yes  
Federal Spec: No  
UL Listing No: UL498  
UL Standard: Yes

UN SPSC: 39121406

UR: No

## DIMENSIONS

Depth (US): 1.08"

Height (US): 3.28"

Width (US): 1.32"

## TECHNICAL INFORMATION

Amps: 15A

Volts: 125V

Volts (AC): 125

Capacity: Single

Grade Type: Federal Specification

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

