



# HEAVY-DUTY SPEC GRADE SINGLE RECEPTACLES, SIDE WIRE RIGHT ANGLE SLOTS, 20A, 125V, BROWN

5371 | Pass & Seymour

#### **FEATURES & BENEFITS**

Heavy-Duty Spec Grade Single Receptacle, Side Wire Right Angle Slots, 20amp 125volt, Brown.



- · Auto-ground clip assures positive ground.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Heavy-duty, corrosion-resistant zinc-plated steel strap fro added strength.
- Backed-out tri-drive steel terminal screws.
- One-piece brass triple-wipe power contacts for lasting retention.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

### **SPECIFICATIONS**

#### **GENERAL INFO**

Color: Brown

Type: Single Receptacles Duty: Heavy Duty

Special Features: Side Wire

### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 No.42

CSA Standard: Yes Federal Spec: No UL Listing No: UL498 UL Standard: Yes UN SPSC: 39121406 UR: No

# **DIMENSIONS**

Depth (US): 0.95" Height (US): 3.28" Width (US): 1.32"

## TECHNICAL INFORMATION

Amps: 20A Volts: 125V Volts (AC): 125 Capacity: Single

Grade Type: Federal Specification

## **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

