



## HEAVY-DUTY SPEC GRADE RECEPTACLES, BACK & SIDE WIRE, 20A, 250V, BROWN

5862 | [Pass & Seymour](#)

### FEATURES & BENEFITS

Heavy-Duty Spec Grade Duplex Receptacle Back & Side Wire 20amp 250volt Brown



- Heavy-duty, brass strap for added strength and ground conductivity.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around face to prevent strap from separating from face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- High strength nylon face.
- Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.
- Eight back wire holes.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

### SPECIFICATIONS

#### GENERAL INFO

Color: Brown  
Type: Receptacles  
Duty: Heavy Duty  
Special Features: Back,Side Wire

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: C22.2 No. 42  
CSA Standard: Yes

Federal Spec: Yes  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121406  
UR: No

#### **DIMENSIONS**

Depth (US): .780"  
Height (US): 3.281"  
Width (US): 1.322"

#### **TECHNICAL INFORMATION**

Amps: 20A  
Volts: 250V  
Volts (AC): 250  
Capacity: Duplex  
Grade Type: Specification

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

