

---

## TOGGLE SWITCH OPENINGS, TWO GANG, 430 STAINLESS STEEL

SL2 | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Smooth Metal Wall Plate, 2gang Toggle, 430 Stainless Steel



- Type 430 Stainless Steel, magnetic: .032" nominal thickness.
- Brushed finish.
- Less corrosion-resistant than Type 302, but ideal for general service in high abuse applications in industrial plants, commercial, and industrial buildings.
- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Size: Standard

Type: Toggle

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: Yes

CUL Listing No: No

cULus: No

cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPSC: 39121704  
UR: No

#### TECHNICAL INFORMATION

Material: 430 Stainless Steel  
Capacity: 2-gang

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant

