



15A, 125V HOSPITAL-GRADE MAXGRIP® M3 PLUG, GRAY

PS8115 | [Pass & Seymour](#)

FEATURES & BENEFITS

Straight Blade Plug 2pole 3wire 15amp 125volt Hospital Grade



- Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements; arc resistance exceeds UL requirements.
- Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws; close hinge housing around cord and tighten housing screws.
- Enclosed terminals provide solid, internally-clamped connections.
- Molded finger grips promote safe, sure handling.
- High-visibility yellow and orange, or gray.
- Hospital Grade version displays the Hospital Grade green dot.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Gray

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
cULus: Yes
cURus: No
Federal Spec: Yes
UL Standard: No
UN SPSC: 39121402
UR: No

DIMENSIONS

Height (US): 1.83"
Width (US): 1.21"

TECHNICAL INFORMATION

Volts (AC): 125
Grade Type: Hospital

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

