



## TAMPER-RESISTANT ISOLATED GROUND HEAVY-DUTY SPEC GRADE RECEPTACLES, ORANGE

TRIG5262 | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Tamper-Resistant Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle, Back & Side Wire, 15amp 125volt, Orange.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Dual mechanical shutter system to help prevent insertion of foreign objects.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Backed-out tri-drive brass terminal screws for faster installation.
- Internal screw-pressure-plate back and side wire capability.
- Two back wire holes for additional wiring flexibility.
- Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.
- .032 inch thick brass triple-wipe power contacts.
- Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Orange  
Type: Receptacles  
Duty: Heavy Duty  
Special Features: Tamper-Resistant, Isolated Ground, Back, Side Wire

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes  
Federal Spec: Yes  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121406

## DIMENSIONS

Depth (US): 1.25"  
Height (US): 3.625"  
Width (US): 1.187"

## TECHNICAL INFORMATION

Amps: 15A  
Volts (AC): 125  
Capacity: Duplex  
Grade Type: Federal Specification

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

