



## TR26242 TAMPER-RESISTANT DECORATOR SPEC GRADE RECEPTACLE, SIDE WIRE ONLY, 15A, 125V, BROWN

TR26242 | [Pass & Seymour](#)

### FEATURES & BENEFITS

Tamper-Resistant Decorator Spec Grade Receptacle, Side Wire Only, 15amp 125volt, Brown

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



- Dual mechanical shutter system to help prevent insertions of foreign objects.
  - High Impact resistant nylon face.
  - Auto-ground clip assures positive ground.
  - Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
  - Backed-out tri-drive steel terminal screws. Side wire only.
  - For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- 
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

### SPECIFICATIONS

#### GENERAL INFO

Color: Brown

Type: Receptacles

Special Features: Tamper-Resistant, side wire only

Style: Decorator

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: Yes

CSA Standard: Yes

cUL Standard: Yes  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121406

#### **DIMENSIONS**

Depth (US): 0.65"  
Height (US): 3.28"  
Width (US): 1.32"

#### **TECHNICAL INFORMATION**

Amps: 15A  
Volts: 125V  
Volts (AC): 125  
Capacity: Duplex  
Grade Type: Specification

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

