



## TRU-UNIVERSAL SINGLE POLE/3-WAY DIMMER, TRI-COLOR

RH703PTUTC | [radiant](#)

### FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

Ideal for typical residential and light commercial applications, the Tru-Universal Dimmer is the simple solution to all your dimming challenges. It works with every 120V dimmable lamp, load, and fixture.

radiant® Screwless Wall Plate not included.

For detailed information on Tru-Universal Dimmers, visit our [Tru-Universal Dimming](#) page.



- Part of the all-new radiant® collection.
- Self-calibration feature allows you to select lamp type, which then automatically sets the minimum voltage for that lamp, eliminating flicker and poor performance.
- Works with every 120V dimmable lamp and load on typical residential and light commercial wiring.
- Convenient operation—combines ON/OFF paddle switch with separate slider for dimming control.
- Wider slide controller for easier dimming operation.
- Preset, single pole and 3-way operation.
- Constant memory returns lights to previous level after a power failure.
- White LED glows when dimmer is OFF for easy location in the dark.
- Rating: Incandescent, Halogen & ELV: 700W, MLV: 500VA, LED/CFL: 450W, EFL: 5.5A (Use RH4FBL3PTC for 0-10V)
- Tru-Universal requires Neutral.
- SSL 7A Compliant
- Comes with three interchangeable face colors: Ivory, White, Light Almond; six additional face cover colors available but sold separately (see HKIT\*).
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## SPECIFICATIONS

SSL 7A Compliant

### GENERAL INFO

Color: Tri-Color (Ivory, White, Light Almond)  
Number Of Poles: Single Pole/3-Way  
Style: Rocker

### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: C22.2 No. 184  
CSA Standard: Yes  
cULus: Yes  
UL Standard: Yes  
UN SPSC: 39121502

### CONSTRUCTION INFORMATION

Component 4: 78500705366

### DIMENSIONS

Depth (US): 1.25"  
Height (US): 4.25"  
Width (US): 1.75"

### TECHNICAL INFORMATION

NEMA Rating: Yes  
Volts: 120  
Volts (AC): 120 VAC, 60Hz  
Watts: 700

### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA