

---

## STERIGUARD™ STRAIGHT BLADE PLUG 20A, 125V

14W33AM | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

"SteriGuard™ Anti-Microbial Wiring Devices provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of Escherichia coli, Gram (-) and Staphylococcus aureus, Gram (+) providing long lasting benefits to manufacturers' beyond conventional cleaning methods. Rated watertight for 1,500 psi high-pressure hosedown, these plugs and connectors feature multiple seals to ensure protection against the environment. SteriGuard provides a cost-effective way to add additional safety precautions and unequaled assurance that every feasible step has been taken in the interest of consumer protection."



- UL and CSA Listed
- NSF (National Sanitation Foundation) Certified
- Patent Pending
- Anti-microbial Additives Embedded in polymer and inhibits Growth of Bacteria, Molds, Mildews and Fungi
- Anti-microbial Additive Resistant to Scuffing and Cleaning
- Escherichia (E.Coli): - Log reduction > 4.8, reduced surface bacteria by > 99.99%
- Staphylococcus (Staph), MRSA: - Log Reduction > 4.3, reduces surface bacteria by > 99.97%
- Salmonella – Log Reduction > 3.6, reduces surface bacteria by > 99.97%
- RoHS Compliant (Non-Halogenated)
- Independently tested and Certified to JIS Z2801 standards
- Resistant to High Pressure Hose-down applications
- Tongue & Groove Environmental Sealing
- Keyed Body and Cover for Alignment
- NEMA Type 4, 4x, 6, 6P and IP67 Protection
- SteriGuard™ Anti-microbial Wiring Devices are ideal for a wide range of applications including food and beverage preparation, procession, & packaging; agriculture, pharmaceutical, and health care.

---

### SPECIFICATIONS

## GENERAL INFO

Color: Yellow  
Type: Plug  
Number Of Poles: 2  
Number Of Wires: 3  
Special Features: Watertight

## LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: Yes  
CSA Listed: Yes  
CSA Standard: Yes  
Federal Spec: Yes  
UL Listing No: E146159  
UL Standard: Yes  
UN SPSC: 39121402

## DIMENSIONS

Diameter (US): 1.63"  
Length (US): 2.68"

## TECHNICAL INFORMATION

Amps: 20A  
Material: Rubber  
NEMA Configuration Number: 5-20  
NEMA Rating: 4X/6P  
Volts: 125V

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant

